



- » 2500 Lumen 26W Samsung SMD LEDs
- » 230v high performance 3m cable & plug
- » Heavy duty housing double epoxy powder coated
- » Weather resistant rear magnetic reed switch
- » Adjustable head for light angle
- » Anti-Slip 'H' foot stand
- » Acrylic LED diffuser for even light dispersion
- » Anti glare tempered glass lens
- » Soft cushion grip handle
- » IPX4 water resistant
- » SL-251 adjustable tripod available (holds 1 or 2 lights)

BATTERY Mains Powered - 230v

WEIGHT 2000g

DIMENSION 300 x 260 x 180 mm



REAR MAGNETIC REED SWITCH



ANTI GLARE TEMPERED GLASS LENS



SMOOTH EVEN LIGHT SPREAD



SL-251 190CM TRIPOD AVAILABLE