




Terminals & Splices > Ring Terminals



Ring Terminal Product Type: Closed Ring Tongue Terminal

Wire Size: 6529 – 10382 CMA

Stud Size: #8, M4

Features

Product Type Features

Shape Description	Circular/Oval
Ring Terminal Product Type	Closed Ring Tongue Terminal
Stud Size	#8, M4
Sealable	No
Compatible With Discrete Wire Type	Stranded
Wire Insulation Support Retention Type	Insulation Support

Configuration Features

Number of Holes	1
-----------------	---

Body Features

Product Weight	1.741 g
----------------	---------

Contact Features

Contact Base Material	Brass
Barrel Type	Open
Terminal Orientation	Straight
Terminal Plating Material	Tin
Contact Underplating Material	Nickel



Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Dimensions

	.15 in
Wire Size	6529 – 10382 CMA
Stud Diameter	4.3 mm [.169 in]
Tongue Thickness	.76 mm [.03 in]
Product Length	24.13 mm [.95 in]
Compatible Insulation Diameter (Max)	5.31 mm [.209 in]
Compatible Insulation Diameter Range	3.8 – 5.3 mm [.15 – .209 in]

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 110 °C [-40 – 230 °F]

Operation/Application

Compatible With Wire Base Material	Copper
------------------------------------	--------

Industry Standards

Government Qualified Terminal	No
-------------------------------	----

Packaging Features

Packaging Quantity	2200
Packaging Method	Strip/Reel

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free



Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 280267-2
COSSE RONDE 12 10



TE Part # 280268-2
RING TONGUE 4-6MM2 0.0276X0.650 TPBR



TE Part # 280261-2
OPEN BARREL RINGTON



TE Part # 2150391-2
OCEAN_2.0_Applicator-E-180F250F-REA




TE Part # 7-2150391-7
OCEAN_2.0_SPARE_PART_KIT-180F250F

Customers Also Bought



TE Part #3-1534798-5
AMP DUOPLUG MK2 CONNECTOR 5P SELECTIVE



TE Part #CAT-C339-A76A
SMD Power Resistor: 2 Watt, 3521 Series



TE Part #1-480700-9
03P UMNL PLUG HSG BLK



TE Part #1-282044-1
AMP MONO-SHAPE P.C.B.CONN4P.G





TE Part #2344656-4
WLAN DUAL BAND ANTENNA FPC V
200mm



TE Part #2112132-1
JPT REC 2.8 Contact SRC Blank



TE Part #1-480701-9
03P UMNL CAP HSG BLK



TE Part #51864-5
TERMINAL,PIDG R 16-14 8



TE Part #3-1879234-1
SMF5 9K1 5%

Documents

Product Drawings
RING TONGUE WITH IS 3.1-5.3 MM2 TPBR
English

CAD Files
Customer View Model
ENG_CVM_CVM_160163-2_O.2d_dxf.zip
English
3D PDF
3D
Customer View Model
ENG_CVM_CVM_160163-2_O.3d_igs.zip
English
Customer View Model
ENG_CVM_CVM_160163-2_O.3d_stp.zip
English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Product Specifications
Application Specification
English