





Technical data

1203S

Double-row self-aligning ball bearings

Self-aligning ball bearing, pressed steel cage, open

VISUAL (S)



1203S

Double-row self-aligning ball bearings

PRODUCT DEFINITION

Brand	NTN
d - Internal diameter	17 mm
D - External diameter	40 mm
B - Bearing/Inner ring width	12 mm
rs - Min fillet radius	0,6 mm
Radial clearance class	CN
Precision class	P0
Mass	0,074 kg

PRODUCT PERFORMANCE

C - Dynamic load	8000000 mN
C0 - Static load	2010000 mN
Cu - Fatigue limit load	83000 mN
e - Coefficient	0.31
Y0 - Static axial load coefficient	2.1
Y1 - Lower axial load coefficient	2
Y2 - Upper axial load coefficient	3.1
N lim - Oil lubrication limit speed	120000 %/s
N lim - Grease lubrication limit speed	96000 %/s
Tmin - Min operating temperature	253,15 °K
Tmax - Max operating temperature	393,15 °K

ABUTMENT

da min - Min shoulder diameter IR	21 mm
Da max - Max shoulder diameter OR	36 mm



NTN Europe

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15

1203S

Double-row self-aligning ball bearings

ABUTMENT

ra max - Max shaft & housing fillet radius

0,6 mm



NTN Europe

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15