



ENGLISH

# Datasheet

## Single Cap with Lead Wire

5ØX20mm



Number	Ampere Rating (in)	Voltage Rating (V)	Nominal Resistance Cold Ohms	Voltage Drop (mv) Max.	Nominal Melting I <sup>2</sup> t A <sup>2</sup> Sec
911-3449	1A	250V	0.0937	1000	1.1151
911-3458	1.25A		0.1420	800	0.8010
911-3451	1.6A		0.0971	600	1.5660
911-3455	2A		0.0642	500	3.5280
911-3464	2.5A		0.0503	400	4.6260
911-3467	3.15A		0.0362	350	9.4050
911-3461	4A		0.0239	300	20.664
911-3470	5A		0.0185	250	27.630
911-3473	6.3A		0.0140	200	68.580
911-3477	8A		0.0098	200	79.488
911-3486	10A		0.0069	200	189.00

### Electrical Characteristics

Rated Current	2.1 in	2.75 in		4 in		10 in
	MAX	MIN	MAX	MIN	MAX	MAX
1A ~ 4A	30 min	10 ms	2 sec	3 ms	300 ms	20 ms
5A ~ 6.3A	30 min	10 ms	3 sec	3 ms	300 ms	20 ms
8A ~ 10A	30 min	40 ms	20 sec	10 ms	1 sec	30 ms

### Interrupting Rating

1500 amperes at 250 V ac

### Operating Temperature

-55°C to +125°C

### Physical Specification

#### Material

Ceramic body / Nickel Plated Brass Caps

Lead Wire: Diameter  $\varnothing$ 0.65mm 6.3A and less.

Diameter  $\varnothing$ 0.8mm 8A/10A

### Dimensions

