




Connectors > Modular Jacks & Plugs > RJ45 Connectors



Modular Jack & Plug Interface Type: **RJ45**

Port Configuration: **Multiple Ports**

Port Matrix Configuration: **1 x 4**

Modular Jacks & Plugs Products: **RJ Type Jacks & Plugs**

Connector Contact Density: **Standard**

Features

Product Type Features

|                                    |                       |
|------------------------------------|-----------------------|
| Connector Product Type             | Connector Assembly    |
| Modular Jack & Plug Interface Type | RJ45                  |
| Modular Jacks & Plugs Products     | RJ Type Jacks & Plugs |
| Modular Connector Style            | Jack                  |
| Grounding Options                  | PCB and Panel Ground  |
| Connector & Contact Terminates To  | Printed Circuit Board |

Configuration Features

|                             |                |
|-----------------------------|----------------|
| Number of PCB Ground Tabs   | 4              |
| Number of Panel Ground Tabs | 12             |
| Multiple Port Configuration | Ganged         |
| Port Configuration          | Multiple Ports |
| Port Matrix Configuration   | 1 x 4          |
| Connector Contact Density   | Standard       |
| Number of Positions         | 8              |
| Number of Loaded Positions  | 8              |
| PCB Mount Orientation       | Right Angle    |

Body Features

|                         |                              |
|-------------------------|------------------------------|
| Shield Plating Material | Copper Preplated with Nickel |
| Shield Material         | Copper Zinc Alloy            |
| LED Color (Top Right)   | Yellow                       |

|                                |                     |
|--------------------------------|---------------------|
| LED Color (Top Left)           | Green               |
| PCB Ground Tab Location        | -3.43 mm[-.135 in]  |
| Modular Jack Latch Orientation | Inverted - Latch Up |
| Connector Profile              | Standard            |

Contact Features

|                                                |                 |
|------------------------------------------------|-----------------|
| Contact Underplating Material                  | Nickel          |
| PCB Contact Termination Area Plating Material  | Tin-Lead        |
| Contact Current Rating (Max)                   | 1.5 A           |
| Contact Mating Area Plating Material           | Gold (Au)       |
| Contact Base Material                          | Phosphor Bronze |
| Contact Mating Area Plating Material Thickness | 3.81 µm[50 µin] |

Termination Features

|                                |                       |
|--------------------------------|-----------------------|
| Termination Method to PCB      | Through Hole - Solder |
| Termination Post & Tail Length | 2.54 mm[.1 in]        |

Mechanical Attachment

|                         |             |
|-------------------------|-------------|
| Panel Mount Feature     | Without     |
| Connector Mounting Type | Panel Mount |

Housing Features

|                       |                                |
|-----------------------|--------------------------------|
| Mating Entry Location | Side                           |
| Centerline (Pitch)    | 1.02 mm[.04 in]                |
| Housing Color         | Black                          |
| Housing Material      | High Temperature Thermoplastic |

Dimensions

|                  |                   |
|------------------|-------------------|
| Connector Height | 13.35 mm[.525 in] |
|------------------|-------------------|

Operation/Application

|                     |        |
|---------------------|--------|
| Indicator Type      | LED    |
| Shielded            | Yes    |
| Circuit Application | Signal |

Industry Standards

|                        |          |
|------------------------|----------|
| UL Flammability Rating | UL 94V-0 |
| Performance Category   | Cat 5    |

Packaging Features



|                    |                  |
|--------------------|------------------|
| Packaging Quantity | 4000             |
| Packaging Method   | Box & Tray, Reel |

Product Compliance

For compliance documentation, visit the product page on TE.com>

|                                               |                                                                                                                               |
|-----------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                                                                                                                     |
| EU ELV Directive 2000/53/EC                   | Not Yet Reviewed                                                                                                              |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold                                                                                       |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JAN 2025 (247)<br>Candidate List Declared Against: JUN 2018 (191)<br>Does not contain REACH SVHC |
| Halogen Content                               | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free                                           |
| Solder Process Capability                     | Wave solder capable to 240°C                                                                                                  |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought

TE Part #5-2176315-6  
MELF SMA\_A 3K3 1% 50PPM 0204 0.4 W

TE Part #2015698-2  
RF CA,UMCC GEN2-GEN2,0.81MM CABLE,L100MM

TE Part #6337194-1  
BATTERY CONNECTOR ASSEMBLY

TE Part #53833-1  
SOLIS SPR SPADE 16-14 8





Documents

CAD Files

3D PDF

English

Customer View Model

ENG\_CVM\_406552-4\_H.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_406552-4\_H.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_406552-4\_H.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Agency Approvals

CSA Certificate

English