

KVR800D2N6K2/4G

**4GB (2GB 256M x 64-Bit x 2 pcs.)
DDR2-800 CL6 240-Pin DIMM Kit**

DESCRIPTION:

ValueRAM's KVR800D2N5K2/2G is a kit of two 256M x 64-bit 2GB (2048MB) DDR2-800 CL6 SDRAM (**S**ynchronous **DRAM**) memory modules. Total kit capacity is 4GB. The components on each module include sixteen 128M x 8-bit DDR2-800 SDRAM in FBGA packages. Each 240-pin DIMM uses gold contact fingers and requires +1.8V. The electrical and mechanical specifications are as follows:

FEATURES:

✓	Clock Cycle Time (tCK) CL=6	2.5ns (min.) / 8ns (max.)
✓	Row Cycle Time (tRC)	60ns (min.)
✓	Refresh to Active/Refresh Command Time (tRFC)	127.5ns
✓	Row Active Time (tRAS)	45ns (min.) / 70,000ns (max.)
✓	Single Power Supply of	+1.8V (+/- .1V)
✓	Power	2.016 W (operating per module)
✓	UL Rating	94 V - 0

Note: The module defined in this data sheet is one of several configurations available under this part number. While all configurations are compatible, the DRAM combination and/or the module height may vary from what is described here.




Figure 1: KVR800D2N6K2/4G 240-Pin DIMM Kit