Features

Hand reamers range are made from heat treaed HSS for ultra-durability, hardness and premium cutting performance and taper to a narrow point for easy entry into the drilled hole

Chemically blackened finish for corrosion resistance

Suitable for use with most ferrous and non-

RS PRO Hand Reamer

RS Stock No.: 456-917



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Hand Reamers

Product Description

RS PRO range of HSS tapered Hand Reamers. The high-quality engineering hand tools are essential when cleaning burrs from a drilled hole, or to make a hole bigger.

General Specifications

Flute	6 Step
Diameter of top/bottom of reamer head	0.20mm/12.10mm
Twist angel for top/bottom individual flute	70 degrees
Overall length of reamer head	85mm (shaft include)
Overall tool length	175mm
Connection Shank Size	6mm (Hexagon shank)

Approvals

Declarations	NA