


**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **5016471000**  
**Status:** **Active**  
**Overview:** iGrid Wire-to-Board Dual-Row System  
**Description:** 2.00mm Pitch iGrid Wire-to-Board Crimp Terminal, Female, Tin (Sn) Plating, 22-26 AWG, Reel

**Documents:**

<a href="#">3D Model</a>	<a href="#">Application Specification 5016460000-A01 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Packaging Specification 5016479200-200 (PDF)</a>
<a href="#">Product Specification PS-501646-001-001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Application Specification 5016460000-A00 (PDF)</a>	



**General**

Product Family	Crimp Terminals
Series	501647
Application	Signal, Wire-to-Board
Crimp Quality Equipment	Yes
Overview	iGrid Wire-to-Board Dual-Row System
Packaging Alternative	501647-1100 (Loose)
Product Name	iGrid
UPC	822350087308

**Physical**

Durability (mating cycles max)	30
Gender	Female
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	76.000/mg
Packaging Type	Reel
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	0.95-1.50mm
Wire Size AWG	22, 24, 26
Wire Size mm <sup>2</sup>	0.124-0.34

**Electrical**

Current - Maximum per Contact	2.0A
Voltage - Maximum	250V AC (RMS)/DC

**Material Info**

**Reference - Drawing Numbers**

Application Specification	5016460000-A00, 5016460000-A01
Crimp Specification	5016470000-CS-000
Packaging Specification	5016479200-200
Product Specification	PS-501646-001-001
Sales Drawing	SD-501647-001

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
ED/61/2018 (27 June  
2018)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

501647 Series

**Use With**

501646 Receptacle Housing

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

Description	Product #
Manual Extraction Tool	<a href="#">638131500</a>
Hand Crimp Tool for 2.00mm Pitch Wire-to-Board Terminals	<a href="#">638192300</a>
T2 Terminator Tooling Die	<a href="#">638587000</a>
FineAdjust Applicator	<a href="#">638687000</a>

**Japan**

Description	Product #
-------------	-----------

Applicator for M211A 5780213000  
Bench Press, 22-26  
AWG Wire  
S-1 Applicator for 5780213700  
iGrid Terminals,  
22-26 AWG,  
0.20-0.30 KV

This document was generated on 11/22/2018

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**