



Passive Components > Resistors > Surface Mount Resistors



Resistance Value: 49.9K Ω

Resistor Type: General Purpose Resistor

Element Type: Thick Film

Package Size Code: 0805

Power Rating: .125 W

Features

Product Type Features

Resistor Type	General Purpose Resistor
Element Type	Thick Film
Package Size Code	0805

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Operating Voltage	150 V
Resistance Value	49.9K Ω
Power Rating	.125 W
Resistance Class	1k Ω – 1M Ω
Passive Component Tolerance	1 %

Termination Features

Surface Mount Resistor Termination Type	Solder
Number of Terminations	2

Dimensions

Product Height	.55 mm[.022 in]
Product Length	2 mm[.079 in]
Product Width	1.25 mm[.049 in]



Usage Conditions

Temperature Coefficient	±100 ppm/°C
-------------------------	-------------

Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) SVHC > Threshold: Pb (24.7% in 4994140) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

CRG0805F49K9

49.9K ohm, Surface Mount General Purpose Resistor, Thick Film, 0805, .125 W, 1 %, ±100 ppm/°C, Solder, 2 Terminations, Neohm CRG



TE Part # 1623404-1
[CRG1206 1% 10K](#)



TE Part # 1622829-1
[CRG0603 1% 10K](#)



TE Part # 1623097-1
[CRG0805 1% 10K](#)



TE Part # 1676480-1
[CRG0402 1% 100K](#)




TE Part # 1-1622826-8
[CRG0402 5% 1K0](#)

Also in the Series | [Neohm CRG](#)



[Surface Mount Resistors\(614\)](#)

Customers Also Bought




TE Part #7-1879648-1
[H4P 287R 0.5% 100PPM](#)



TE Part #9-1625971-5
[HSA25 R01 10%](#)




TE Part #7-1879354-5
[RR03 5% 390R AMMO](#)




TE Part #2337238-3
[TACT MINI GW 5.2X5.2X2 160GF](#)



TE Part #1-830611-0
[LGH 1/2 SNGL MLD END](#)



TE Part #3-2176307-2
[RP 1E 0.1W 26K1 0.1% 25PPM 5K RL](#)



TE Part #3-1437162-8
[FSP-12A-11](#)



TE Part #1-1879353-9
[RR02 5% 24K AMMO](#)



Documents

Product Drawings

CRG0805 1% 49K9

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1623225-8_BA.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1623225-8_BA.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1623225-8_BA.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Thick Film Chip Resistors - Type CRG series

English