




Connectors > Lighting Connectors > Plug & Socket Lighting Connectors



Number of Positions: 2

Lighting Connector Style: **Plug**

Connector Product Type: **Housing**

Operating Voltage: **42 VAC**

Features

Product Type Features

Lighting Connector Style	Plug
Connector Product Type	Housing

Configuration Features

Keying Arrangement	LV-1
Number of Positions	2

Electrical Characteristics

Operating Voltage	42 VAC
-------------------	--------

Body Features

Primary Product Color	Light Gray
-----------------------	------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2018 (181) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free




Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought




**ANVIL** REPRESENTATION ONLY


TE Part #2-1803002-6  
ANVIL



TE Part #7-2834182-2  
1P,PLUG CABLE ASSY-203.2MM,  
WHITE,TIN




TE Part #2150719-1  
OCEAN\_2.0\_Applicator-E-180F-REM




**ANVIL** REPRESENTATION ONLY

TE Part #3-1633919-6  
ANVIL COMBINATION




**ANVIL** REPRESENTATION ONLY


TE Part #1803337-2  
ANVIL, COMBINATION




TE Part #2-32510-1  
TERMINAL,PIDG SPD FLG 12-10 8




TE Part #1-2379237-1  
NECTOR T, INLINE SOCKET, SCREW,  
Key-A,S2



TE Part #1-2379238-1  
NECTOR T, INLINE PIN, SCREW, Key-  
A, S2



TE Part #2266508-2  
OCEAN\_2.0\_Applicator-S-070F120OA-  
RSA



TE Part #1586378-1  
03P UMNL CAP HSG NATL

Documents

Product Drawings  
NECTOR S PLUG LV-1 GRAY  
English



CAD Files

Customer View Model  
[ENG\\_CVM\\_1740449-1\\_E.3d\\_igs.zip](#)  
English

Customer View Model  
[ENG\\_CVM\\_1740449-1\\_E.3d\\_stp.zip](#)  
English

Customer View Model  
[ENG\\_CVM\\_1740449-1\\_E.2d\\_dxf.zip](#)  
English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[NECTOR\\_S\\_LINE\\_CONNECTOR\\_BROCHURE](#)  
English