



Impact Wrench XGT®, TW010G

40Vmax, 1", 3,150 Nm

Model TW010G is a 1" square drive D-handle impact wrench powered by a 40Vmax XGT® Li-Ion battery

Model TW010G is equipped with a long anvil. Main Feature and benefits: Auto-stop system available in both forward/reverse rotation modes. Trigger switch with full speed mode. High torque / Excellent manoeuvrability.



Technical specifications

Voltage XGT	✓
Nominal Battery Voltage	40 V
Brushless Motor	✓
No load speed	0 - 600 / 700 / 850 / 1200 min ⁻¹
Max Fastening Torque Impact Drill	600 / 1000 / 1600 / 3150 Nm
Nut-busting torque	4000 Nm
Tightening Capacity Standard Bolt	M27 - M45
Tightening Capacity High Tensile Bolt	M20 - M33
Impacts per Minute (IPM)	0 - 1200 / 1300 / 1500 / 1750 min ⁻¹
Drive Square	1 "
Sound Power Level (L _{WA})	111 dB(A)
Sound Pressure Level (L _{pA})	103 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)

User benefits

- Electronic 4 stage impact power selection for added versatility
- 3 modes of reaction time for automatic stop available both in forward and reverse rotation modes
- Brushless maintenance-free and long-life motor
- Side handle swivels 360° for greater control
- LED light illuminates the work site
- Electric brake for maximum productivity and increased operator safety
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions

Link to product - www.makitauk.com



Related products

Other

User manual

Parts drawing