



Residual current circuit breaker (RCCB), 25A, 2pole, 30mA, type AC

Part no. PFGM-25/2/003
Article no. 264266
Catalog No.



Technical data ETIM 5.0

Circuit breakers and fuses (EG000020) / Residual current circuit breaker (RCCB) (EC000003)			
Electric engineering, automation, process control engineering / Electrical installation, device / Residual current protection system / Residual current circuit breaker (RCCB) (ecI@ss8-27-14-22-01 [AAB906010])			
Number of poles			2
Rated voltage		V	230
Rated current		A	25
Rated fault current		A	0.03
Mounting method			DIN-rail (DRA)
Leakage current type			AC
Selective protection			No
Short-circuit breaking capacity (Icw)		kA	10
Rated short-circuit breaking capacity EN 60898		kA	0.5
Rated short-circuit breaking capacity IEC 60947-2		kA	0
Surge current capacity		kA	0.25
Frequency			50 Hz
Additional equipment possible			Yes
Degree of protection (IP)			IP20
Construction size (in accordance with DIN 43880)			1
Width in number of modular spacings			2
Built-in depth		mm	69.5
Short-time delayed tripping			No