



DCF885M2

18 XR Li-Ion Compact Impact Driver

Features

- Latest generation 18V XR Li-Ion Compact Impact Driver featuring NEW XR 4.0Ah Li-Ion battery technology
- Ultra compact, lightweight design allows for use in confined spaces
- Improved ergonomic design and rubber grip increase comfort
- Improved ergonomic design and rubber grip increase comfort
- Improved ergonomic design and rubber grip increase comfort
- Part of the intelligent XR Lithium Ion Series designed for efficiency and making applications faster
- Intelligent trigger allowing total control over all applications
- 6.35mm 'drop in' keyless hex driver allows for quick, one handed fitment
- Bright white LED ring with delay feature for improved visibility and flashlight functionality
- All metal gearing for efficient power transmission and long tool life
- Aluminium front housing provides greater heat dispersion increasing motor life
- Steel belt clip and strong magnetic bit holder ensure storage solutions
- Multi-voltage charger for use with 18V, 14.4V, and 10.8V XR Li-Ion slide pack batteries

Standard Equipment

- Multi-voltage charger
- 2 slide batteries
- Heavy duty kit box

Warranty Specifications

- 3 Year Limited Warranty
- 30 Day Money Back Guarantee
- 1 Year Free Service Contract

Specifications	
Voltage	18 V
Battery Capacity	4.0 Ah
Bit Holder	1/4" (6.35mm)
Power Output	250 Watts
No Load Speed	2800 rpm
Impacts per Minute	3200 ipm
Max Torque	155 Nm
Max. Bolt Diameter	M12
Weight	1.6 kg
Length	141 mm
Height	236 mm
Hand/Arm Vibration - Impact	15.5 m/s ²
Uncertainty K 1 (Vibration)	2.2 m/s ²
Sound Pressure	90 dB(A)
Uncertainty K 1 (Sound)	3 dB(A)
Accoustic Pressure	101 dB(A)
Uncertainty K 2 (Sound)	3 dB(A)
Battery chemistry	Li-ion