



ENGLISH

## Datasheet

# RS Lithium Thionyl Chloride AA Battery

RS Stock 778-1100



## Benefits

- High voltage response, stable during most of the lifetime of the application
- Wide operating temperature range (60°C/+85°C)
- Low self-discharge rate (less than 1 % after 1 year of storage at + 20°C)
- Easy integration into compact systems
- Superior resistance to atmospheric corrosion

## Key features

- Stainless steel container and end caps (low magnetic signature)
- Hermetic glass-to-metal sealing
- Non-flammable electrolyte
- Underwriters Laboratories (UL) Component Recognition
- Compliant with IEC 60086-4 safety standard and IEC 60079-11 intrinsic safety standard
- Restricted for transport (Class 9)

## Main applications

- Utility metering
- Automatic meter readers
- Buoys
- Measuring equipment
- Industrial applications
- Professional electronics

**Electrical characteristics**

*(typical values relative to cells stored for one year or less at + 30°C max.)*

Nominal capacity <i>(at 4 mA +20°C 2.0 V cut-off. The capacity restored by the cell varies according to current drain, temperature and cut-off)</i>	7.7 Ah
Open circuit voltage (at +20°C)	3.67 V
Nominal voltage (at 0.5 mA + 20°C)	3.6 V
Nominal energy	27.72 Wh
Pulse capability: Typically up to 300 mA <i>(300 mA/0.1 second pulses, drained every 2 mn at +20°C from undischarged cells with 10 µA base current, yield voltage readings above 3.0 V. The readings may vary according to the pulse characteristics, the temperature, and the cell's previous history. Fitting the cell with a capacitor may be recommended in severe conditions. Consult Saft)</i>	
Maximum recommended continuous current <i>(Higher currents possible, consult Saft)</i>	150 mA
Storage (recommended) <i>(for more severe conditions, consult Saft)</i>	+ 30°C (+ 86°F) max
Operating temperature range <i>(Operation above ambient T may lead to reduced capacity and lower voltage readings at the beginning of pulses. Consult Saft)</i>	- 60°C/+ 85°C (- 76°F/+ 185°F)

**Physical characteristics**

Diameter (max)	26.0 mm (1.02 in)
Height (max)	49.1 mm or 50.4 mm (1.93 in or 1.98 in) depending on finish type
Typical weight	48 g (1.7 oz)
Li metal content	approx. 2.0 g
Available termination suffix	
CNR	radial tabs
3 PF, 3 PF RP	radial pins
CNA (AX)	axial leads
FL	flying leads... etc.