



### Main

Range of product	Ovalis
Product or component type	Switch
Device application	Light control
Device presentation	Complete product
Type of packing	Flow-pack
Quantity per set	10 pieces
Sale per indivisible quantity	1
Colour tint	White (RAL 9003)

### Complementary

Device mounting	Flush
Switch function	1-pole 2-way
Number of rocker	2
Actuator	Rocker
Fixing mode	By screws and claws
Switch pattern	[6+6]
Surface finish	Matt
Rated current	10 AX at 250 V AC 50/60 Hz
Load type	Load for energy saving lamps with ballast: 100 W
Minimum load breaking capacity	200 operations 1.25 In and 1.1 Un with $\cos \varphi = 0.3$
Service life in cycles	20000 Cycles at ON and OFF at rated voltage with $\cos \varphi = 0.6$ 20000 cycles at 5 In ON + In OFF
Electrical durability	20000 cycles
Shape of screw head	Pozidriv No 1
Clamping connection capacity	1 x 1.5...2 x 2.5 mm <sup>2</sup> for rigid cable(s) 1 x 1.5...2 x 2.5 mm <sup>2</sup> for flexible cable(s) 1 x 1.5...2 x 2.5 mm <sup>2</sup> for stranded cable(s)
Wire stripping length	12 mm
Material	Thermoplastic ABS-UV stabilised: centre plate PBT (polybutylene terephthalate) GF30: support frame PC (polycarbonate) GF10 FR: casing
Height	87 mm
Width	87 mm
Depth	33.4 mm
Embedding depth	26.5 mm
Net weight	0.045 kg

### Environment

Ambient air temperature for storage	-5...50 °C
Dielectric strength	2000 V
Ambient air temperature for operation	5...35 °C
Standards	EN 60669-1 2006/95/EEC
Product certifications	LCIE[RETURN]NF
IK degree of protection	IK04

IP degree of protection	IP21D
Environmental characteristic	Liquid soap UV resistant Bleach Oil Window-cleaning fluid Acetone Petrol Alcohol

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations