

# POLYAMIDE (PA) FLEXIBLE TUBING

[✉ Email](#)[🖨 Print](#)

Tried-and-tested for industrial or vehicle applications, PA tubing guarantees excellent durability due to its stable long-term mechanical properties.  
Special grade of semi-rigid polyamide manufactured according to our Eco-Design approach.

**PART NUMBER:**

1025P14 00

**TUBING MATERIAL:**

PA

**TUBE I.D. (MM):**

12

**TUBE O.D. (MM):**

14

**COLOR:**

NATURAL

**LENGTH (M):**

25

[Reset Attributes](#)**WHERE TO BUY**

PRODUCT OVERVIEW	-
TECH SPECIFICATIONS	+

[Print Tech Specifications](#)

PERFORMANCE CHARACTERISTICS

MAXIMUM PRESSURE (BARG)

50

MINIMUM WORKING TEMPERATURE (°C)

-40

MAXIMUM WORKING TEMPERATURE (C)

100

VACUUM RATING (MM OF HG)

755

WEIGHT (KG/PACKAGE)

1.535

MAXIMUM BEND RADIUS (MM)

116

NUMBER OF TUBES

1

APPLICATION

Packaging, Tooling, Compressed Air, Motion Technologies,  
Robotics, Industrial Machinery

MEDIA

Semi-Rigid PA: Compressed air, other fluids /Rigid PA:  
Compressed air,lubricants, other fluids

CERTIFICATES

Industrial: DI: 2002/95/EC (RoHS), 2011/65/EC; DI: 97/23/EC  
(PED); RG: 1907/2006 (REACH)/Transportation: Chemical  
performance and resistance tested according to DIN 74324 -1 /  
DIN 73378 / ISO 7681

[Print Tech Specifications](#)

PRODUCT SUPPORT	+
-----------------	---

RECOMMENDED



lencers



Stainless Steel Non-  
Return Valves



Pneumatic Sensor  
Fittings



Pneumatic Pilot  
Non-Return Valve

CONTACT US

Parker Hannifin Manufacturing France SAS

Fluid System Connectors Division Europe  
Parc Alcyone - Bat. D  
1 rue André et Yvonne Meynier - CS 46911  
35069 Rennes Cedex France

Phone

Phone: +33 (0) 2-99-25-55-00



EMAIL PARKER

Parker Hannifin



Products

About Parker

Investors

Community

Careers

Global Operations



Divisions

Sales Companies

Worldwide Locations

Distribution Network

ParkerStore™ Network

Company Information

