

Product Information Sheet

COMMISSION DELEGATED REGULATION (EU) 2019/2015 with regard to energy labelling of light sources

Supplier's name or trade mark: LED2WORK GmbH.

Supplier's address: Vertrieb, Stuttgarter Straße 13A, 75179 Pforzheim, DE

Model identifier: 2941-5022-00-LE-215p

Type of light source:

Lighting technology used:	LED	Non-directional or directional:	DLS
Light source cap-type (or other electric interface)	-		
Mains or non-mains:	NMLS	Connected light source (CLS):	No
Colour-tuneable light source:	No	Envelope:	-
High luminance light source:	No		
Anti-glare shield:	No	Dimmable:	Only with specific dimmers

Product parameters

Parameter	Value	Parameter	Value
-----------	-------	-----------	-------

General product parameters:


Energy consumption in on-mode (kWh/1000 h), rounded up to the nearest integer	9	Energy efficiency class	C
Useful luminous flux (ϕ_{use}), indicating if it refers to the flux in a sphere (360°), in a wide cone (120°) or in a narrow cone (90°)	1 399 in Wide cone (120°)	Correlated colour temperature, rounded to the nearest 100 K, or the range of correlated colour temperatures, rounded to the nearest 100 K, that can be set	5 700
On-mode power (P_{on}), expressed in W	8,7	Standby power (P_{sb}), expressed in W and rounded to the second decimal	0,00
Networked standby power (P_{net}) for CLS, expressed in W and rounded to the second decimal	-	Colour rendering index, rounded to the nearest integer, or the range of CRI-values that can be set	95
Outer dimensions without separate control gear, light-	Height	6	Spectral power distribution in the range 250 nm to 800 nm, at full-load
	Width	215	
	Depth	14	
			See image in last page

ing control parts and non-lighting control parts, if any (millimetre)			
Claim of equivalent power ^(a)	-	If yes, equivalent power (W)	-
		Chromaticity coordinates (x and y)	0,324 0,346
Parameters for directional light sources:			
Peak luminous intensity (cd)	779	Beam angle in degrees, or the range of beam angles that can be set	113
Parameters for LED and OLED light sources:			
R9 colour rendering index value	83	Survival factor	-
the lumen maintenance factor	-		


(a)¹⁾ : not applicable;

(b)¹⁾ : not applicable;

Spektrale Strahlungsverteilung
Spectral power distribution



Model placed on the Union market from 22/11/2024



EPREL registration number: 2192524

<https://eprel.ec.europa.eu/qr/2192524>

Supplier: LED2WORK GmbH (Manufacturer)

Website: led2work.com

Customer care service:

Name: Vertrieb

Website: www.led2work.com

Email: info@led2work.com

Phone: +49 7231 44920-00

Address:

Stuttgarter Straße 13A
75179 Pforzheim
Germany