



### Characteristics:

- Allows thorough cleaning of ESD sensitive assemblies without the danger of high charges generated by conventional brushes
- Conductive carbon loaded polypropylene handle
- Permanent static dissipative bristles, made of Nylon 6.12, superior grade, high quality Nylon filament
- Yellow bristles, 0.4mm in diameter
- Highly resilient, durable and abrasion resistant
- For cleaning ESD sensitive assemblies
- Hot stamped ESD protective symbol
- RTG: 10E9 - 10E10 Ohms



Designed to fulfill ANSI/ESD S20.20 requirement to ground all conductors at ESD workstation.

ESD Handbook TR20.20 Table 1 lists under Typical Static Electricity Sources "Brushes (camel/pig hair and synthetic bristles)."

"It should be understood that any object, item, material or person could be a source of static electricity in the work environment. Removal of unnecessary nonconductors, replacing nonconductive materials with dissipative or conductive materials and grounding all conductors are the principle methods of controlling static electricity in the workplace, regardless of the activity." (TR 20.20 section 2.4)

Item	Handle Type	Overall Length*
35685	Round	6.1" (15.5 cm)
35686	Flat	5.9" (15.0 cm)
35687	Flat	6.6" (16.8 cm)
35688	Long	7.0" (17.8 cm)
35689	Curved	3.95" (10.0 cm)

\*Dimensions are taken from the bottom of the brush to the top of the bristles.

### Dissipative Brushes

# MENDA

3651 WALNUT AVE., CHINO, CA 91710  
PHONE: (909) 627-2453 • FAX: (951) 755-8848  
WEBSITE: [MendaPump.com](http://MendaPump.com)

DRAWING NUMBER  
35685

DATE:  
August  
2007