

EB-W05

DATASHEET / BROCHURE



For home or work, this easy-to-use, 3,300-lumen WXGA projector with optional Wi-Fi can create a 320-inch display.

Do you love the big-screen experience, but also need a projector that will deliver striking presentations? This WXGA projector with 3,300 lumens of brightness and 3LCD technology has the tools for the job. Designed with portability in mind, it's easy to transport and set up. It's competitive too, with a fantastic range of features and a long lamp life providing 15 years' worth of entertainment¹.

Bigger is better

Whether you're watching blockbusters or delivering a presentation, this projector can achieve an impressive 320-inch display. It's great quality too, with 3LCD technology that makes the display up to three times brighter than competitor products². In addition to its bright and vivid colours, the 15,000:1 contrast ratio produces defined shadows and deep blacks. From family and friends to business colleagues and clients, it's sure to get everyone's attention.

High-quality, bright images

Even in bright rooms, this powerful yet affordable WXGA projector delivers exceptionally bright yet colourful images with clear details. It's all thanks to 3LCD technology, which produces an equally high White and Colour Light Output of 3,300 lumens.

Long-lasting solution

Looking for a long-term, hassle-free and affordable solution for your projection needs? With this model's long-lasting lamp light source, you could watch a film every day for 15 years¹.

Stress-free set up

Here's a projector that's designed with portability and quick set up in mind. Position the image with keystone correction and access content simply with the HDMI inputs. Thanks to the optional ELPAP10 adapter, it offers Wi-Fi connectivity allowing you to share content from a smart device using the iProjection app.

KEY FEATURES

- **Create the big screen experience**
From box sets to business presentations, capture everyone's attention
- **Bright even with ambient light**
Equally high White and Colour Light Output of 3,300 lumens
- **Affordable, high-tech equipment**
Enjoy this WXGA projector
- **Long-lasting solution**
Watch a film every day for 15 years¹
- **Portable and quick to set up**
Easy to position with keystone slider



EPSON[®]
EXCEED YOUR VISION

EB-W05

WHAT'S IN THE BOX

- Main unit
- Power cable
- Quick Start Guide
- Remote control incl. batteries
- User manual (CD)
- Warranty card
- Computer cable

OPTIONAL ACCESSORIES

- Wireless LAN Adapter - ELPAP10
V12H731P01
- ELPLP96
V13H010L96
- Air Filter - ELPAF32
V13H134A32
- Soft Carry Case - ELPKS69 - EB-x05/x41/x42, EH-TW6 series
V12H001K69
- Ceiling Pipe (700mm) - ELPFP14
V12H003P14
- Ceiling Pipe (450mm) - ELPFP13
V12H003P13
- Ceiling Mount (White) - ELPMB23
V12H003B23

LOGISTICS INFORMATION

SKU	V11H840041
EAN code	8715946639505
Country of Origin	Philippines
Layer	6 Units
Layer Block	6 Units

EB-W05



For more information please contact:

Home users: 0343 90 37766
Business users*: 0871 42 37766
Republic of Ireland: 01 436 7742
Or visit us at <https://www.epson.co.uk/contactus>
* 10p per minute plus network extras.

Web: www.epson.co.uk
www.epson.ie

Trademarks and registered trademarks are the property of Seiko Epson Corporation or their respective owners.
Product information is subject to change without prior notice.
Last extracted: 2020-06-19

1. Based on watching an average 1hr 45mins film every day and with the lamp set in Eco mode.
2. Colour brightness (Colour Light Output) in brightest mode, measured by a third-party lab in accordance with IDMS 15.4. Colour brightness will vary depending on usage conditions. Top-selling Epson 3LCD projectors versus top selling 1-chip DLP projectors based on PMA research sales data for Dec 2015 through Nov 2016.

EPSON[®]