

Technical characteristics

Limiting temperature	-40 ... +100 °C
Flammability acc. to UL 94	V-0
Degree of protection acc. to IEC 60529	IP68, IP69K
Material (seal)	NBR
Material (cable glands)	Polyamide

Technical characteristics

Colour (accessories)	RAL 5012 (light blue), RAL 9005 (jet black), RAL 7032 (pebble grey), RAL 7035 (light grey)
----------------------	--

Specifications and approvals




Identification	Size	Clamping range (mm)	Part number	Drawing (dimensions in mm)
----------------	------	---------------------	-------------	----------------------------

Han® CGM-Ex i ,
Cable gland,
Intrinsically safe electric circuits
Blue

M20	5 ... 9
M20	6 ... 12
M25	9 ... 16
M32	13 ... 20
M40	22 ... 32

19 00 000 7101
19 00 000 7102
19 00 000 7104
19 00 000 7106
19 00 000 7109



Han® CGM-P ,
Cable gland,
Grey



M20	5 ... 9
M20	6 ... 12
M20	10 ... 14
M25	9 ... 16
M25	13 ... 18
M32	13 ... 18
M32	18 ... 25
M40	20 ... 26
M40	22 ... 32

19 00 000 5180
19 00 000 5182
19 00 000 5184
19 00 000 5190
19 00 000 5192
19 00 000 5194
19 00 000 5196
19 00 000 5197
19 00 000 5198

Outer cable Ø	SW	E	Nm
5 ... 9 mm	24	26.4	4.5
6 ... 12 mm	24	26.4	4.5
10 ... 14 mm	27	29.8	4.5
9 ... 16 mm	33	33.5	5
13 ... 18 mm	33	36.5	5
13 ... 20 mm	42	46.8	6.5
18 ... 25 mm	42	46.8	6.5
20 ... 26 mm	53	58.8	10
22 ... 32 mm	53	58.8	10

Han® CGM-P ,
Cable gland,
Black



M20	5 ... 9
M20	6 ... 12
M20	10 ... 14
M25	9 ... 16
M25	13 ... 18
M32	13 ... 20
M32	18 ... 25
M40	20 ... 26
M40	22 ... 32

19 00 000 5181
19 00 000 5183
19 00 000 5185
19 00 000 5191
19 00 000 5193
19 00 000 5186
19 00 000 5187
19 00 000 5188
19 00 000 5189

Accessories