




Wire & Cable > Twisted Pair Cable > Outer Space 2 Core Cable: Tin Coated Copper



Operating Temperature Range: -65 – 150 °C [-85 – 302 °F]

Cable Type: **Spec 55**

Operating Voltage: **600 VAC**

Wire & Cable Insulation Material: **Modified Radiation Cross-linked ETFE Polymer**

Conductor Material: **Tin-Coated Copper**

[All Outer Space 2 Core Cable: Tin Coated Copper \(7\)](#)

Features

Electrical Characteristics

Operating Voltage	600 VAC
-------------------	---------

Body Features

Wire & Cable Insulation Material	Modified Radiation Cross-linked ETFE Polymer
Conductor Material	Tin-Coated Copper

Dimensions

Wire Size	20 AWG
-----------	--------

Usage Conditions

Operating Temperature Range	-65 – 150 °C[-85 – 302 °F]
Cable Type	Spec 55

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	



Current ECHA Candidate List: JAN 2025
(247)
Candidate List Declared Against: JUNE
2024 (241)
Does not contain REACH SVHC

Halogen Content	Out of Scope - excluded from Halogen requirements
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 650075-000
D-436-37

Customers Also Bought



TE Part #228311-000
HEX40-AC-00-21-A9-1-DS



TE Part #109761-000
44A0141-20-9/90/92/96




TE Part #BTH1-15-08-1-ZN
BTH1-15-08-1-ZN




TE Part #387811-000
44A1111-20-4-9



TE Part #CV5805-000
HEX40-AC-00-23-A13-2



TE Part #2-1589483-7
STL065L2HN = SMT CONN



TE Part #C31298-000
55PC0121-22-2/6



TE Part #70A1-20-16-1-B
70A1-20-16-1-B



TE Part #E146163001
55A9012-30-4/5



TE Part #A05444-000
TXR41AB45-2008BI

Documents

55/2121-20-2/6-9

English

Datasheets & Catalog Pages

Raychem Wire and Cable Quick Reference Guide

English

Product Specification

English