
## **CFL Series: Can & Fingered Lid**

A range of standard and custom RFI/EMI cans that offer good attenuation and accessibility where screening of complete boards or circuits is required.

- Removable Fingered Lid giving easy access and excellent attenuation
- ♦ Lid Fingering Clearance
  selective fingers can be omitted for clearance
  around components mounted through the frame wall
- Component/PCB Locations (optional) lancings or brackets can be specified to act as guides or supports (see back page)
- Butt Jointed Corners bright acid tin finish allows corners to be easily soldered for increased screening
- Internal Dividers (optional) for discrete screening within the can (see page 7)
- Custom Sizes

   can be manufactured without tooling charges making prototypes and low volumes viable
- Additional Features
   holes, brackets, cut outs, lid captivation, etc., can be incorporated during manufacture (see back page)
- ♦ Alternative Materials/Finishes copper, brass, tinplate, nickel, nickel plate



## Specification

Material:
Bright Mild Steel
BS EN 10130 DC01
Frames:
20swg (0.914mm)
Lids:
24swg (0.559mm)
Finish:
Bright Acid Tin:
Good Commercial Grade

**Surface resistivity:**  $20 \times 10^{-6} \Omega$  per square


Conductivity:

**Tolerance:** +/\_ 0.25mm (general)

## STOCK SIZES - Internal & overall dimensions (mm)

Part No.	Dimension A	Dimension B	Dimension C	Nominal overall size including lid
CFL5⊤	20	20	10	25 x 25 x 12
CFL6⊤	30	30	15	35 x 35 x 17
CFL7⊤	50	25	15	55 x 30 x 17
CFL1⊤	50	50	15	55 x 55 x 17
CFL2⊤	75	50	25	80 x 55 x 27
CFL8⊤	75	75	25	80 x 80 x 27
CFL3⊤	100	50	35	105 x 55 x 37
CFL4⊤	160	100	50	165 x 105 x 52

NOTE: A4 dimensioned drawings for each part are available on request.



5 x 10<sup>4</sup>S (mho)

PERANCEA LTD

Telephone: 020-8365 2520 Email: sales@perancea.com Fax: 020-8365 3727 Page 5 Website: www.perancea.com