

KEMET Part Number: PHE450KB6100JR17
(F450BJ104J400A)

PHE450/F450, Film, Double Metallized Polypropylene, General Purpose, 0.1 uF, 5%, 400 VDC, 85°C, Lead Spacing = 15mm



Dimensions

L	18mm MAX
H	12.5mm MAX
T	6.5mm MAX
S	15mm +/-0.4mm
LL	17mm -1mm
F	0.8mm +/-0.05mm
G	0.5mm NOM

Packaging Specifications

Packaging:	Bulk, Bag
Packaging Quantity:	600

General Information

Supplier:	KEMET
Series:	PHE450/F450
Dielectric:	Double Metallized Polypropylene
Style:	Radial
Features:	Pulse
RoHS:	Yes
Lead:	Wire Leads
AEC-Q200:	No
Miscellaneous:	The Rated Voltage Decreases 1.3%/C Between +85C And +105C. Rthja= 85 C/W (85C), 0.2 m/s

Specifications

Capacitance:	0.1 uF
Capacitance Tolerance:	5%
Voltage AC:	250 VAC
Voltage DC:	400 VDC (85C), 296 VDC (105C)
Temperature Range:	-55/+105°C
Rated Temperature:	85°C
Dissipation Factor:	0.03% 1kHz, 0.04% 10kHz, 0.15% 100kHz
Insulation Resistance:	300 GOhms
Max dV/dt:	1000 V/us
Inductance:	6 nH