



CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes

more than you expect





TERM. NO.'s FOR REF. ONLY



DOT LOCATES TERM. #1

LOT CODE & DATE CODE



**ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:**

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	1-3 @20°C	0.315 ohms ±10%
D.C. RESISTANCE	6-4 @20°C	7.95 ohms ±10%
INDUCTANCE	1-3 100kHz, 100mVAC, L <sub>s</sub>	60uH ±15%
SATURATION CURRENT	20% rolloff from initial	250mA
LEAKAGE INDUCTANCE	1-3 tie(4+6), 100kHz, 100mVAC, L <sub>s</sub>	1.0uH max.
DIELECTRIC	1-6 1500VAC, 1 second	-
TURNS RATIO	(6-4):(1-3)	5:1, ±1%

**GENERAL SPECIFICATIONS:**

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

Wire insulation & RoHS status not affected by wire color.  
Wire insulation color may vary depending on availability.

DETAILS SUBJECT TO CHANGE

REV.	DATE	Packaging Specifications Method: <b>Tape &amp; Reel</b> PKG-0637 www.we-online.com/midcom		Tolerances unless otherwise specified: Angles: ±1°      Decimals: ±.005 [.13] Fractions: ±1/64      Footprint: ±.005 [.13]	DRAWING TITLE <b>TRANSFORMER</b>	PART NO. <b>750311691</b>
6A	11/10	SEE REVISION SHEET FOR REVISION LEVEL	CONVENTION PLACEMENT	This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750311691	compliant RoHS SPECIFICATION SHEET 1 OF 1