

FEATURES

- **Graphite and PTFE material:** Offers superior chemical resistance and durability
- **Maximum operating pressure of 8500 kPa:** Suitable for high-pressure applications
- **Maximum operating temperature of 280 °C:** Ensures reliable performance in high-temperature environments
- **Rotary speed of 28 m/s:** Compatible with fast-moving machinery
- **Section size of 5 mm:** Fits a variety of gland and valve configurations

RS PRO 8m Gland & Valve Packing, Graphite PTFE

RS Stock No: 606-561



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO gland and valve packing is designed for high-performance sealing applications. Made from a combination of graphite and polytetrafluoroethylene, it provides excellent resistance to high temperatures and pressures, making it ideal for demanding industrial environments.

General Specifications

Maximum Operating Pressure	8500 kPa
Product Type	Gland & Valve Packing
Rotary Speed	28 m/s
Section	5 mm
Sub Type	Gland Packing

Mechanical Specifications

Length	8 m
Material	Graphite, Polytetrafluoroethylene

Operation Environment Specifications

Maximum Operating Temperature	280 °C
-------------------------------	--------

Approvals

Standards/Approvals	ANSI-ESD S20.20:2021, RoHS
---------------------	----------------------------