



## Main

Range	Ovalis C Series
Product or component type	TV socket
Device presentation	Complete product
TV socket type	Individual socket
Colour tint	White (RAL 9003)
Type of packing	Flow-pack
Quantity per set	1
Sale per indivisible quantity	1

## Complementary

Device mounting	Flush
TV connector	Male IEC 9.52 mm
Path attenuation	1.5 DB TV signal5...1800 MHz 2.5 dB TV signal1800...2150 MHz
Fixing mode	By claws By screws
Surface finish	Matt
Connections - terminals	Screw terminals
Shape of screw head	Pozidriv No 1
Wire stripping length	8 mm
Type of cable	Coaxial
Cable outer diameter	7 mm
Material	Thermoplastic ABS-UV stabilised: centre plate PBT (polybutylene terephthalate) GF30: support frame Zinc alloy: casing Thermoplastic ABS-UV stabilised: cover frame
Height	87 mm
Width	87 mm
Depth	27 mm
Embedding depth	18.1 mm
Net weight	0.045 kg
Condition of use	Indoor

## Environment

Ambient air temperature for storage	-5...50 °C
Ambient air temperature for operation	5...45 °C
Standards	EN 50083-4
IK degree of protection	IK04
IP degree of protection	IP21D
Environmental characteristic	Bleach Liquid soap Window-cleaning fluid Alcohol Acetone Oil UV resistant Petrol

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
Minimum percentage of recycled plastic content	0