

Start Waterproof LED G3 fixed output

START Waterproof Twin 1200 IP65 4800lm 865
0067964



Product features

- Start Waterproof, integrated LED weatherproof luminaire, with UV stabilized flat diffuser and linear prisms designed to achieve uniform lit appearance, optimise light output and to reduce glare, stainless steel diffuser clips and fixing brackets for surface mounting. Polycarbonate housing, Polycarbonate diffuser, 4800 lm, 38 W, 127 lm/W, 6500 K, drive current 1050 mA, non dimmable, CRI80, IP65, IK08, Class I, nominal average lifetime (h): 50000, 1278 mm x 110 mm x 78 mm, energy class: A++ A+ A, D-mark



PRODUCT OVERVIEW

IPC Code	0067964
Product name	START Waterproof Twin 1200 IP65 4800lm 865
Technology	LED
Housing	Polycarbonate
Mount	Ceiling Mounting and Suspended Mounting
Fixture rating	Enclosed
General application	Logistics & Industry
Certifications	EUNEW009
ETIM Class	EC002892
Fixture luminous flux (lm)	4800
Luminaire efficacy (lm/W)	120
Colour temperature (K)	6500
Light colour	Daylight
CRI (Ra)	80
Photobiological Risk Group	RG1
Total power consumption (W)	40
Electrical protection	Class I
Control gear type	Electronic (constant current)
Dimmable	No
Average life (Nominal) (h)	50000
Housing colour	Grey
IP rating	IP65
IK rating	IK08
Product EAN number	5410288679648
Lamps	Yes
Included lamp	INTEGRATED LED

DATA TABLE

General data

IPC Code	0067964
Product name	START Waterproof Twin 1200 IP65 4800lm 865
Technology	LED
Housing	Polycarbonate
Mount	Ceiling Mounting and Suspended Mounting

Start Waterproof LED G3 fixed output

START Waterproof Twin 1200 IP65 4800lm 865
0067964

Fixture rating	Enclosed
General application	Logistics & Industry
Operating temperature range (°C)	-20°C...+40°C
Certifications	EUNEW009
ETIM Class	EC002892

Optical data

Fixture luminous flux (lm)	4800
Luminaire efficacy (lm/W)	120
Colour temperature (K)	6500
Light colour	Daylight
CRI (Ra)	80
Distribution type	Direct
Photobiological Risk Group	RG1

Electrical data

Total power consumption (W)	40
Mains voltage (V)	220-240V~
Lamp power factor	0.95
THD (at 230 V, 50 Hz, full load, at 100% dimming level) xx.x %	20
Electrical protection	Class I
Control gear required	No
Control gear type	Electronic (constant current)
Dimmable	No
Drive current (mA)	1050
Nominal Frequency (Hz)	50/60Hz

Lifetime data

Lumen maintenance - L70 B50	60000
Lumen maintenance - L70 B20	60000
Lumen maintenance - L70 B10	60000
Lumen maintenance - L80 B50	60000
Lumen maintenance - L80 B20	60000
Lumen maintenance - L80 B10	60000
Lumen maintenance - L90 B50	59000
Lumen maintenance - L90 B20	53000
Lumen maintenance - L90 B10	50000
Average life (Nominal) (h)	50000

Physical data

Housing colour	Grey
IP rating	IP65
IK rating	IK08
Diffuser finish	Clear
Diffuser material	Polycarbonate
Nominal Product Length (mm)	1278
Nominal Product Width (mm)	110
Nominal Product Height (mm)	78

Start Waterproof LED G3 fixed output START Waterproof Twin 1200 IP65 4800lm 865 0067964

Weight (kg)	1.82
-------------	------


Packaging

Single packaging type	Carton
Product EAN number	5410288679648
Packaging single length / height (cm)	137.2
Packaging single width (cm)	11.6
Packaging single depth (cm)	8.4
DUN14 (outer)	05410288679648
Units per outer package	1
Packaging outer length / height (cm)	137.2
Packaging outer width (cm)	11.6
Packaging outer depth (cm)	8.4

Safety data

Dry applications use only	No
---------------------------	----

PHOTOMETRY



Distance [m]	Cone diameter [m]	E ₀ [lx]	E ₁ (C90) [lx]	E ₂ (C0) [lx]
0.5	1.20 1.46	6431	503*	554*
1.0	2.41 2.91	1608	251*	146*
1.5	3.61 4.37	715	93*	65*
2.0	4.82 5.82	402	62*	37*
2.5	6.02 7.28	257	34*	23*
3.0	7.23 8.73	179	23*	15*


Distance [m] Cone diameter [m] Illuminance [lx]
 C0 - C180 (Half beam angle: 111.0°)
 C90 - C270 (Half beam angle: 100.6°)


TECHNICAL DRAWINGS




Start Waterproof LED G3 fixed output *START Waterproof Twin 1200 IP65 4800lm 865* 0067964


SYLVANIA 0067964


 This luminaire contains built-in LED lamps

 } LED


The lamps cannot be changed in the luminaire.

874/2012 

 This luminaire contains built-in LED lamps

 } LED

The lamps cannot be changed in the luminaire.

SYLVANIA 0067964 

874/2012