

AMP Signal Double Lock

TE Internal #: 2321922-4


Wire Seal, -30 – 105 °C [-22 – 221 °F], Blue, Silicone Rubber, 4

Position, AMP Signal Double Lock

[View on TE.com >](#)



Connectors > Connector Accessories > Connector Seals & Cavity Plugs > Connector Seals: 2.55 mm, Signal Double Lock



Connector Seal & Plug Type: **Wire Seal**
Operating Temperature Range: -30 – 105 °C [-22 – 221 °F]
Primary Product Color: **Blue**
Primary Product Material: **Silicone Rubber**
Operating Temperature (Max): 105 °C [221 °F]

[All Connector Seals: 2.55 mm, Signal Double Lock \(10\)](#)

Features

Product Type Features

Connector Seal & Plug Type	Wire Seal
----------------------------	-----------

Configuration Features

Number of Positions	4
---------------------	---

Body Features

Primary Product Color	Blue
Primary Product Material	Silicone Rubber

Usage Conditions

Operating Temperature Range	-30 – 105 °C[-22 – 221 °F]
Operating Temperature (Max)	105 °C[221 °F]

Packaging Features

Packaging Method	Bag
------------------	-----

Product Compliance



For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2321920-4
PERIMETER SEAL PLUG HOUSING
4PIN



TE Part # 2321918-4
PLUG HOUSING SDL2.5
WATERPROOF 4PIN

Also in the Series | [AMP Signal Double Lock](#)



Connector Caps & Covers(1)

Connector Contacts(14)

Connector Hardware(19)

Connector Seals & Cavity Plugs(10)

Insertion & Extraction Tools(1)

PCB Headers & Receptacles(146)

Rectangular Power Connectors(46)

Wire-to-Board Headers & Receptacles (146)

Customers Also Bought

TE Part #2295044-6
RITS CONN. PLUG ASSY 6P YELLOW
TIN

TE Part #CAT-526SDL-SEALHS
Sealed Connector Housings: 2.5 mm,
Signal Double Lock

TE Part #2273051-1
M12 Male pnl Mld Rear Mt PG9 pigt A

TE Part #CAT-526SDL-SEALTM
Sealed Connector: Terminals, Signal
Double Lock, 2.5 mm

TE Part #EH2301-000
DWFR-52/13-0-STK

TE Part #CAT-526SDL-SEALTP
Sealed Connector: TPAs, Signal
Double Lock, 2.5 mm

TE Part #2321920-3
PERIMETER SEAL PLUG HOUSING
3PIN

Documents

Product Drawings
REAR WIRE SEAL 4PIN

English

- CAD Files
- 3D PDF
- 3D
- Customer View Model
- ENG_CVM_CVM_2321922-4_A.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_2321922-4_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2321922-4_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[2-1773983-6_Sealed_Signal_Double_Lock](#)

English

Product Specifications

[Application Specification](#)

English

Instruction Sheets

[Instruction Sheet \(non U.S.\)](#)

English

[Instruction Sheet \(non U.S.\)](#)

English