






ITEM #	PART #	REV	DESCRIPTION	QTY	Material	Weight
1	MDA050	01	Nozzle body	1	Aluminium	10.4g
2	PA6063	02	Wide Angle Valve Assy.	1		6.7g
3	PA6062	02	Wide angle valve cap	1	Aluminium	9.3g
4	FOZ005	02	O Ring	1	Viton	0.1g



SECTION A-A

REL-03	FOZ028 & FOZ005 'O' Rings were removed to stop problems with air flow.	27/11/2009
REV.	DESCRIPTION	DATE

 Power Adhesives THIS DRAWING AND THE INFORMATION IT CONTAINS IS THE PROPERTY OF POWER ADHESIVES AND IS CONFIDENTIAL. IT MUST NOT BE REPRODUCED EITHER WHOLLY OR IN PART. ALL RIGHTS IN RESPECT OF PATENTS, DESIGNS AND COPYRIGHTS ARE RESERVED.	MATERIAL		DRAWN	SteveE	DIMENSIONS ARE IN MM UNLESS OTHERWISE STATED  THIRD ANGLE	TOLERANCES UNLESS OTHERWISE STATED WHOLE NUMBERS ±0.5mm 1 DECIMAL PLACE ±0.3mm 2 DECIMAL PLACE ±0.1mm	SCALE 1:1
	FINISH		DATE				SHEET 1 OF 2
	COLOUR		ECR No.	00036	TITLE		Wide Spray Nozzle Assy - 2mm
	NOTES						
						DWG. No.	MPN - PA6064
					A4		03

1	2	3	4	5	6					
A	Technical data									
	Type	Hot melt applicator nozzle								
	Material composition	Aluminium, steel, music wire, viton rubber								
	Weight	26.7g (0.94 oz)								
	Thread size	3/8 UNF								
	Nozzle hole size	2mm (0.08")								
	Spring rate	0.73 N/mm (4.15 lb/inch)								
B										
C										
D	 THIS DRAWING AND THE INFORMATION IT CONTAINS IS THE PROPERTY OF POWER ADHESIVES AND IS CONFIDENTIAL. IT MUST NOT BE REPRODUCED EITHER WHOLLY OR IN PART. ALL RIGHTS IN RESPECT OF PATENTS DESIGNS AND COPYRIGHTS ARE RESERVED.		MATERIAL		DRAWN	SteveE	DIMENSIONS ARE IN MM UNLESS OTHERWISE STATED  THIRD ANGLE	TOLERANCES UNLESS OTHERWISE STATED WHOLE NUMBERS ±0.5mm 1 DECIMAL PLACE ±0.3mm 2 DECIMAL PLACE ±0.1mm	SCALE 1:1	
			FINISH		DATE				TITLE Wide Spray Nozzle Assy - 2mm	
			COLOUR		ECR No.	00036	DWG. No. A4	PA6064		REVISION 03
			NOTES							
			1	2	3	4	5	6		