



Hand crimping tool for preinsulated products



1 to 2.5 mm²

- ✓ Crimping of blue perinsulated terminals, disconnects, pins, blades and window butt connectors from 1.0 to 2.5 mm²
- ✓ Aluminium body
- ✓ Exceptional low gearing
- ✓ High quality crimping by linear movement of dies
- ✓ Adjustable crimping of cable insulation by eccentric
- ✓ Safety ratchet
- ✓ Positioner stopper
- ✓ Crimping dies identification reference mark : 2 dashes

Delivered in individual box with control and instruction leaflet

- ✓ Length : 290 mm
- ✓ Weight : 0.490 Kg

TH 2 : delivered with stopper HF20 for terminals, disconnects, pins and blade terminals

p/n

TH2

SNCF

7-847-7141



TH 2 S : delivered with stopper HF20 for terminals, disconnects, pins and butt connectors

p/n

TH2S

SNCF

7-847-7141

Complementary accessory :

- ✓ PG 2 : go-no go gauge

Hand crimping tool for preinsulated products



1 to 6 mm²

- ✓ Strong and practical steel tools
- ✓ High quality crimping by linear movement of dies
- ✓ Adjustable crimping of cable insulation by a pin
- ✓ Safety ratchet
- ✓ Positioner stopper ATH23
- ✓ Crimping dies identification reference mark : 3 dots

Delivered in individual box with control and instruction leaflet

- ✓ Length : 290 mm - Weight : 0.905 Kg.
- ✓ Handles colour : TH3 = 1 yellow and one white - TH3-2 : one yellow and one black

TH3 : max. insulating diameter : 6.8 mm

- ✓ Crimping of white terminals 51190 series and disconnects from 1 to 2.5 mm²
- ✓ Crimping of yellow terminals C3P series and disconnects from 2.6 to 6 mm²

p/n

TH3

SNCF

7-847-7142



TH3 : max. insulating diameter : 8.8 mm

- ✓ Crimping of black terminals 51190 series and disconnects from 1 to 2.5 mm²
- ✓ Crimping of yellow black stripped terminals C3P series and disconnects from 2.6 to 6 mm²

p/n

TH3-2

SNCF

7-847-7143 ou 0-391-6837



Complementary accessory :

- ✓ PGH3 : go-no go gauge