






Figure 1 is a plan view of the test section of the bridge deck. It shows a cross-section of the bridge deck with a central section labeled "DDT JAE" and a section to the right labeled "A". The deck is supported by a central pier and two side piers. The width of the deck is indicated as 24, and the height of the deck is indicated as ± 0.2 . The diagram includes various structural details such as reinforcement bars, concrete walls, and a central pier. Arrows point from "NOTE 2" to the side piers.



注1.端子寸法は0.05^{±0.05}であり公差内におけるバラツキ(1コネクタ内のMAX値とMIN値の差)は0.1以下とする。

- 2.図示の位置に社標“JAE”“キヤピ No.”及び品名“DD1”を表示する。
- 3.ランドは基板の両側に設けること。また、スルーホール穴はスルーホールメッキであること。
- 4.図に示す範囲をパターン禁止領域とする。

4	THROUGH HOLE PLATE	2	COPPER ALLOY	NICKEL PLATING THROUGH HOLE AREA:TIN PLATING	
3	SHELL	1	STAINLESS STEEL	NICKEL PLATING THROUGH HOLE AREA:TIN PLATING	
2	INSULATOR	1	9T NYLON	BLACK	UL94 V-0
1	CONTACT	30	COPPER ALLOY	CONTACT AREA:GOLD OVER NICKEL SMT AREA:GOLD FLASH OVER NICKEL	GOLD:0.1μm MIN GOLD FLASH:0.03~0.1μm
符号 NO.	名 称 DESCRIPTION	個 数 QTY.	材 料 MATERIAL	仕 上 FINISH	備 考 REMARKS
仕様書 (SPECIFICATION) JACS-3285		第1版 (ORIGINAL DATE) 12.Nov.2004		尺 寸 (SCALE) S: 1	シリーズ (SERIES) DD1
一般公差 (GENERAL TOLERANCE)		製図 DR.	担当 CHK. Y.KUROKI 査閲 APPD. _____ 承認 APPD. O.HAGA	名 称 (TITLE) DD1B030VA1	日本航空電子工業株式会社 JAPAN AVIATION ELECTRONICS INDUSTRY, LTD. 
寸法 (DIMENSION)	角度 (ANGLES)				
. ±	×° ±				
.×× ±	×°×' ±				
.××× ±				質量 (MASS)	
図面番号 (DRAWING NO.) SJ102068					