



Article No. : 1FL2204-2AF01-0SC0

Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :

Basic motor data

Motor type	Permanent-magnet synchronous motor
Motor type	Medium Inertia
Static torque	2.40 Nm
Static current	2.25 A
Maximum torque	7.50 Nm
Maximum current	7.1 A
Maximum speed	6,500 rpm
Rotor moment of inertia	1.2300 kgcm ²
Weight	2.6 kg

Rated data

SINAMICS S200, 3 AC 380 ... 480 V

Rated speed	3,000 rpm
Rated torque	2.40 Nm
Rated current	2.2 A
Rated power	0.75 kW

Encoder system

Encoder system	Absolute encoder singleturn 21 bit
----------------	------------------------------------

Motor connection

Connection type	Metal hybrid connector
-----------------	------------------------

Mechanical data

Design acc. to Code I	IM B5 (IM V1, IM V3)
Vibration severity grade	Grade A
Shaft height	40
Flange size (AB)	81 mm
Centering ring (N)	70 mm
Hole circle (M)	90 mm
Screw-on hole (S)	6.6 mm
Overall length (LB)	124.6 mm
Diameter of shaft (D)	19 mm
Length of shaft (E)	40 mm
Length of flange diagonal (P)	104.9 mm
Shaft end	Plain shaft
Color of the housing	Anthracite RAL 7016

