



Product data sheet

Power tools for trade & industry

Thermo Camera

PRO GTC 400 C



Immediate visualisation of temperature differences with smart documentation

The most important data

Measurement range	-10 °C to +400 °C
Measuring accuracy of IR	±3.0 °C
Resolution	0.1 °C

Part Number 0 601 083 108

Technical data

Technical data

Battery voltage	12.0 V
Measurement range	-10 °C to +400 °C
Measuring accuracy of IR	±3.0 °C
Resolution	0.1 °C
Thermal sensitivity (NETD)	<50 mK
Size of IR sensor	160 Pixel x 120 Pixel
Number of measuring points	19,200
Field of view (FOV)	53° x 43°
Power supply and runtime	4 x 1.5 V LR6 (AA), 1 x GBA 12V, 1 x GBA 10.8V
Frame buffer (number of images)	500
Memory type	Internal memory
File format of image	.jpg
Data transfer	MicroUSB, Wi-Fi
Dust and splash protection	IP 53
Weight	0.54 kg
Size of display	3.5"
Operating temperature	-10 – 45 °C
Storage temperature	-20 – 70 °C
Focus distance, minimum	0.3 m
Net weight	0.357 kg
Gross weight	2.567 kg



BOSCH

Invented for life

Product data sheet

Power tools for trade & industry

Advantages:

- Fast exchange of data and easy documentation of thermal images with the Bosch ThermalOn app
- Picture-in-picture technology overlays thermal and real images for easy-to-see localisation of the measurement
- Flexible battery system can be powered by a 12 V LI-ION battery or with standard alkaline batteries



You can find more information about the deviations in the following link: <https://www.bosch-professional.com/gb/en/wac/>

