


Retro-reflective sensor

OUP-DPKG



receiver in upper lens
transmitter in lower lens



Product characteristics

Type of light	red light
Housing	rectangular

Application

Special feature	polarisation filter
Function principle	Retro-reflective sensor

Electrical data

Operating voltage	[V]	10...55 DC
Current consumption	[mA]	30; ((24 V))
Protection class		II
Reverse polarity protection		yes
Type of light		red light
Wave length	[nm]	660

Outputs

Electrical design		PNP
Output function		dark-on mode
Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	250
Switching frequency DC	[Hz]	160
Short-circuit protection		yes
Type of short-circuit protection		pulsed
Overload protection		yes

Detection zone


Range referred to prismatic reflector	[m]	0.15...1.5; (Prismatic reflector Ø 80 E20005)
Range adjustable		yes
Max. light spot diameter	[mm]	475
Light spot dimensions refer to		at maximum range
Polarisation filter available		yes



Retro-reflective sensor

OUP-DPKG

Operating conditions		
Ambient temperature	[°C]	-25...60
Protection		IP 67
Tests / approvals		
EMC	EN 60947-5-2	
	EN 55011	class B
MTTF	[years]	687
Mechanical data		
Weight	[g]	150
Housing		rectangular
Dimensions	[mm]	28 x 16 x 51
Materials		PPO modified
Lens material		glass
Lens alignment		side lens
Displays / operating elements		
Display	switching status	1 x LED, yellow
Accessories		
Items supplied		Angle bracket: 1, E20211
Remarks		
Pack quantity		1 pcs.
Electrical connection		
Cable: 2 m, PVC; 3 x 0.34 mm²		
Connection		



BN	brown
BU	blue
BK	black

Retro-reflective sensor

OUP-DPKG

Diagrams and graphs

excess gain graph

