



Main

| | |
|---------------------------|-------------------------|
| Range of product | PowerPact multistandard |
| Range | PowerPact |
| Product name | L-Frame |
| Device short name | L-Frame |
| Product or component type | Circuit breaker |
| Device application | Distribution |

Complementary

| | |
|--|--|
| Poles description | 3P |
| Control type | Toggle |
| Mounting mode | Unit mount |
| Mounting support | DIN rail Flush Backplate |
| Electrical connection | Lugs, line side Lugs, load side |
| Wire Size | 1 x AWG 2/0...500 kcmil (aluminium/copper) |
| [In] rated current | 400 A at 40 °C |
| [Ui] rated insulation voltage | 750 V AC 50/60 Hz conforming to IEC 60947-2 |
| [Uimp] rated impulse withstand voltage | 8 kV conforming to IEC 60947-2 |
| [Ue] rated operational voltage | 525 V AC 50/60 Hz conforming to IEC 60947-2 690 V AC 50/60 Hz conforming to IEC 947-2 600 V AC 50/60 Hz conforming to UL 489 |
| Breaking capacity code | D |
| Suitability for isolation | Yes |
| Utilisation category | Category A |
| Mechanical durability | 5000 cycles |
| Electrical durability | 1000 cycles |
| Connection pitch | 45 mm |
| Local signalling | ON/OFF indication |
| Contact position indicator | Yes |
| Trip unit name | MicroLogic 3.3 |
| Trip unit technology | Electronic |
| Trip unit protection functions | LI |
| Trip unit rating | 400 A |
| Thermal memory | 20 mn |
| Display type | 3 LEDs |
| Breaking capacity | Icu: 25 kA at 220/240 V - AC conforming to IEC 947-2 Icu: 18 kA at 380/415 V - AC conforming to IEC 947-2 Icu: 18 kA at 440/480 V - AC conforming to IEC 947-2 Icu: 14 kA at 500/525 V - AC conforming to IEC 947-2 25 KA at 240 V - AC conforming to UL 489 18 KA at 480 V - AC conforming to UL 489 14 kA at 600 V - AC conforming to UL 489 |

| | |
|--|--|
| [Ics] rated service breaking capacity | Ics: 25 kA at 220/240 V - AC conforming to IEC 947-2 Ics: 18 kA at 380/415 V - AC conforming to IEC 947-2 Ics: 18 kA at 440/480 V - AC conforming to IEC 947-2 Ics: 14 kA at 500/525 V - AC conforming to IEC 947-2 |
| Long time pick-up adjustment type Ir | Adjustable 9 settings |
| Long time pick-up adjustment range | 0.33...1 x In |
| [tr] long-time delay adjustment range | 1 S 0.5 S 2 S 8 S 4 S 16 s |
| Instantaneous pick-up adjustment type li | Adjustable 9 settings |
| Instantaneous pick-up adjustment range | 1.5...15 x In |
| Overvoltage category | II |
| Provision for padlocking | Non padlockable |
| Height | 340 mm |
| Width | 140 mm |
| Depth | 110 mm |
| Standards | UL 489 NEMA AB1 W-C-375B/GEN NMX J-266 CSA C22.2 No 5 IEC 60947-2 |
| Product certifications | CE[RETURN]CCC |
| Net weight | 6.2 kg |

Environment

| | |
|---------------------------------------|--|
| IP degree of protection | IP40 conforming to IEC 60529 |
| IK degree of protection | IK07 conforming to IEC 62262 |
| Pollution degree | 3 conforming to IEC 60947-1 3 conforming to IEC 60664-1 |
| Ambient air temperature for operation | 40 °C |
| Ambient air temperature for storage | -50...85 °C |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation |  REACH Declaration |
| EU RoHS Directive | Compliant with Exemptions |
| Mercury free | Yes |
| RoHS exemption information |  Yes |
| China RoHS Regulation |  China RoHS Declaration |
| Environmental Disclosure |  Product Environmental Profile |
| Circularity Profile |  End Of Life Information |