



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



TE Part #2118651-6
RF CA,UMCC GEN1-GEN1,1.13MM,
L90MM,GREY



TE Part #1623728-4
BCHE 11 W 150R 5%



TE Part #1-1734248-6
1.0 FPC, ZIF V/T, SMT, 16P



TE Part #5499923-8
A/L UNIV HDR 34P VERT LAT



TE Part #6-1879745-4
[RP 1J 2K49 0.1% 15PPM CUT LENGTH](#)

TE Part #4-1393224-5
[RY211009](#)

TE Part #057233-000
[202D242-25/225-0](#)

TE Part #2-1445084-2
[micro mnl hdr assy s/row au lf](#)

TE Part #1483350-3
[MICRO-MATCH LEAD 04P 250MM](#)

TE Part #1-1393558-3
[C42334A 422C334=BKMOD 422 BUEG](#)

Documents

Product Drawings

[C42334A 422C316=BKMOD 422 BUEG](#)

English

[C42334A 422C316=BKMOD 422 BUEG](#)

English