

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [39-00-0430](#)  
**Status:** **Active**  
**Overview:** Mini-Fit Jr.™ Power Connectors  
**Description:** Mini-Fit® Male Crimp Terminal, Brass, Gold (Au) Contact Plating, Lead-free, 18-24 AWG, Reel

**Documents:**

<a href="#">Drawing (PDF)</a>	<a href="#">Product Specification PS-5556-002 (PDF)</a>
<a href="#">Product Specification PS-51010-007 (PDF)</a>	<a href="#">Test Summary TS-5556-002 (PDF)</a>
<a href="#">Product Specification PS-52034-005 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>

**General**

Product Family	Crimp Terminals
Series	5558
Application	Power
Crimp Quality Equipment	Yes
Overview	<a href="#">Mini-Fit Jr.™ Power Connectors</a>
Packaging Alternative	<a href="#">39-00-0431 (Loose)</a>
Product Name	Mini-Fit®
UPC	822348149384

**Physical**

Durability (mating cycles max)	30
Gender	Male
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Net Weight	0.126/g
Packaging Type	Reel
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.30-3.10mm
Wire Size AWG	18, 20, 22, 24
Wire Size mm²	N/A

**Electrical**

Current - Maximum per Contact	9A
Voltage - Maximum	600V

**Material Info**

Old Part Number	5558-GS7F
-----------------	-----------

**Reference - Drawing Numbers**

Product Specification	PS-51010-007, PS-52034-005, PS-5556-002
Sales Drawing	SD-5558-002
Test Summary	TS-5556-002



**EU RoHS**

**ELV and RoHS Compliant**  
**REACH SVHC Contains SVHC: No**  
**Low-Halogen Status Low-Halogen**

**China RoHS**



**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**

[5558Series](#)

**Mates With**

[5556 Mini-Fit® Crimp Terminal](#)

**Use With**

[5559 Mini-Fit Jr.™ Plug Housing](#)

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

Description	Product #
Hand Crimp Tool for Male and Female Crimp Terminals, 16-24 AWG Wire	<a href="#">0638190900</a>
FineAdjust™ Applicator for Insulation OD	<a href="#">0639023900</a>

1.40-1.70mm - 18-24  
AWG  
T2 Terminator™ for 0639102900  
insulation OD 1.65  
– 2.05mm – 18 – 24  
AWG  
T2 Terminator™ 0639123900  
for insulation OD  
1.40-1.70mm - 18-24  
AWG  
FineAdjust™ 0639024800  
Applicator for  
Insulation OD  
2.50-2.95mm  
Optimized for 18  
AWG Only  
T2 Terminator™ 0639115600  
for insulation OD  
1.90-2.30mm - 18-24  
AWG  
Extraction Tool 0011030044  
FineAdjust™ 0639002600  
Applicator for  
Insulation OD  
2.50-2.95mm - 18-24  
AWG  
FineAdjust™ 0639002900  
Applicator for  
Insulation OD  
1.65-2.05mm - 18-24  
AWG  
T2 Terminator™ 0639102600  
for insulation OD  
2.50-2.95mm - 18-24  
AWG  
T2 Terminator™ 0639124800  
for insulation OD  
2.50-2.95mm  
optimized for 18  
AWG only  
FineAdjust™ 0639015600  
Applicator for  
Insulation OD  
1.90-2.30mm - 18-24  
AWG  
FineAdjust™ 0639024900  
Applicator for  
Insulation OD  
2.30-2.60mm - 18-24  
AWG  
T2 Terminator™ 0639124900  
for insulation OD  
2.30-2.60mm - 18-24  
AWG

This document was generated on 12/18/2014

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**