



Passive Components > Inductors > High Frequency & RF Inductors



Inductor Type: **High Frequency**
Package Size Code: **0402**
Inductance: **.0019 μ H**
Current Rating (Max): **560 mA**
DC Resistance: **.35 Ω**

Features

Product Type Features

Inductor Type	High Frequency
Package Size Code	0402
Element Type	Thin Film

Electrical Characteristics

Self Resonant Frequency	8 GHz
Inductance	.0019 μ H
Current Rating (Max)	560 mA
DC Resistance	.35 Ω
Passive Component Tolerance	.2 %

Termination Features

Termination Method to PCB	Surface Mount
---------------------------	---------------

Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------

Other

Inductor Quality Factor	13
-------------------------	----

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------



EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



TE Part #2-1445057-2
MICRO MNL HDR ASSY SINGLE ROW



TE Part #6-2176422-9
TLRP 2512 3.0W R068 1% 50PPM 4K RL



TE Part #747845-4
15 MSFL RCPT RA 318 (IN,FM,BL)



TE Part #1879011-1
SMF2 220R 5%



TE Part #640456-8
08P MTA100 HDR ASSY F/L SQ STR



TE Part #2041262-1
Mini PCI-E 6.8H G/F



TE Part #5553813-3
ASSY,EMI RCPT,50 POSN,SCR LK



TE Part #5555154-1
MJ,R/A,LPF,6P/6C,SHLD,PNL,TRAY

Documents

CAD Files

36401E1N9ATDF

3640 0402 1.9nH +/-0.2nH 1K RL



Customer View Model

[ENG_CVM_CVM_4-1624108-2_BA.2d_dxf.zip](#)

English

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_4-1624108-2_BA.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_4-1624108-2_BA.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1309350_PASSIVE_COMPONENT](#)

English

[High Frequency Inductors SMD - Type 3640 Series](#)

English