



Cut-off wheel EHT 125x1.0x22.23 mm flat Performance Line SG STEELOX for steel/stainless steel

Cut-off wheel EHT 125x1.0x22.23 mm flat Performance Line SG STEELOX for steel/stainless steel

Item number: [61341112](#)

EAN: [4007220499733](#)

The broad range Performance Line SG offers a high-performance tool solution for every application and every material. Performance Line SG tools achieve optimum results with maximum economic efficiency.

Cut-off wheel for steel and stainless steel (INOX) with high cutting performance and maximum tool life.

Workers all over the world rely on quality and therefore choose the thin cut-off wheels from PFERD TOOLS. The PFERD TOOLS product range includes thin cut-off wheels in various designs and therefore the right tool solution for any application – ergonomically optimized, efficient and with the highest level of safety. The thin cut-off wheels from PFERD TOOLS are characterized by their special bond formulation. Intensive research and development work combined with systematic implementation in state-of-the-art production facilities guarantee PFERD TOOLS' high quality and safety standards.

Technical information

Abrasive	Aluminium oxide A
Dia. external	125 mm
Dia. hole	22.23 mm
Dia. hole, additional	without
Max. RPM	12200 RPM
Mounting system	Centre hole
PFERD TOOLS type	EHT 125-1,0 SG STEELOX
Shape	EHT / 41 / T1
Width	1 mm

Advantages

- ✔ Suitable for general use on steel and stainless steel (INOX).
- ✔ Fast work progress thanks to good cutting performance.
- ✔ Maximum economic efficiency due to maximum tool life.
- ✔ Thin cuts with minimal burr formation.
- ✔ Convenient and safe.
- ✔ Fast cutting.

Materials that can be worked

- ✔ Stainless steel (INOX)
- ✔ Steel

Applications

- ✔ Cutting of profiles
- ✔ Cutting of sheet metal
- ✔ Cutting of solid material
- ✔ Cutting out holes

Drive types

- ✔ Angle grinder
 - ✔ Drive spindle
-



August Rüggeberg GmbH & Co. KG
Hauptstraße 13
51709 Marienheide

+49 2264 9-0

+49 2264 9-400

info@pferd.com