

# MBR3035CT - MBR30150CT

30.0 AMPS. Schottky Barrier Rectifiers



## **TO-220AB**




### **Features**


- Plastic material used carries Underwriters Laboratory Classifications 94V-0
- ♦ Metal silicon junction, majority carrier conduction
- ♦ Low power loss, high efficiency
- High current capability, low forward voltage drop
- High surge capability
- For use in low voltage, high frequency inverters, free wheeling, and polarity protection applications
- ♦ Guardring for overvoltage protection
- High temperature soldering guaranteed: 260°C/10 seconds,0.25"(6.35mm)from case
- Green compound with suffix "G" on packing code & prefix "G" on datecode.

#### **Mechanical Data**

- ♦ Cases: JEDEC TO-220AB molded plastic
- Terminals: Pure tin plated, lead free, solderable per MIL-STD-750, Method 2026
- ♦ Polarity: As marked
- Mounting position: Any
- ♦ Mounting torque: 5 in. lbs. max
- ♦ Weight: 0.08 ounce, 2.24 grams



Dimensions in inches and (millimeters)



## **Maximum Ratings and Electrical Characteristics**

Rating at 25 °C ambient temperature unless otherwise specified. Single phase, half wave, 60 Hz, resistive or inductive load.

For capacitive load, derate current by 20%

Type Number	Symbol	MBR 3035 CT	MBR 3045 CT	MBR 3050 CT	MBR 3060 CT	MBR 3090 CT	MBR 30100 CT	MBR 30150 CT	Units
Maximum Recurrent Peak Reverse Voltage	Vrrm	35	45	50	60	90	100	150	V
Maximum RMS Voltage	VRMS	24	31	35	42	63	70	105	V
Maximum DC Blocking Voltage	VDC	35	45	50	60	90	100	150	V
Maximum Average Forward Rectified Current at T <sub>C</sub> =130°C	I(AV)	30							Α
Peak Repetitive Forward Current (Rated V <sub>R</sub> , Square Wave, 20KHz) at Tc=130°C	FRM	30							А
Peak Forward Surge Current, 8.3 ms Single Half Sine-wave Superimposed on Rated Load (JEDEC method)	İFSM	200							А
Peak Repetitive Reverse Surge Current (Note 1)	IRRM	1.0			0.5			Α	
Maximum Instantaneous Forward Voltage at (Note 2)  I <sub>F</sub> =15A, Tc=25°C  I <sub>F</sub> =30A, Tc=25°C  I <sub>F</sub> =30A, Tc=125°C	VF			0. 0. -		0. 0.	84 70 94 82	0.95 0.92 1.02 0.98	٧
Maximum Instantaneous Reverse Current @ Tc=25 °C at Rated DC Blocking Voltage Per Leg @ Tc=125 °C (Note 2)	lr		).2 I5		).2  0		).2 '.5	0.1 5.0	mA mA
Voltage Rate of Change, (Rated V <sub>R</sub> )	dV/dt	10,000						V/uS	
Typical Junction Capacitance @4V 1.0 MHz	Cj	600 460			60	320			pF
Maximum Thermal Resistance Per Leg (Note 3)	Rејс	1.0 1.5					°C/W		
Operating Junction Temperature Range	TJ	-65 to +150						°C	
Storage Temperature Range	Tstg	-65 to +175							°C

Notes: 1. 2.0us Pulse Width, f=1.0 KHz

2. Pulse Test: 300us Pulse Width, 1% Duty Cycle

3. Thermal Resistance from Junction to Case Per Leg, with Heatsink size (4"x6"x0.25") Al-Plate

Version: E09



#### RATINGS AND CHARACTERISTIC CURVES (MBR3035CT THRU MBR30150CT)

FIG.1- FORWARD CURRENT DERATING CURVE




FIG.2- MAXIMUM NON-REPETITIVE FORWARD SURGE CURRENT PER LEG




FIG.3- TYPICAL INSTANTANEOUS FORWARD CHARACTERISTICS PER LEG




FIG.4- TYPICAL REVERSE CHARACTERISTICS




FIG.5- TYPICAL JUNCTION CAPACITANCE PER LEG




FIG.6- TYPICAL TRANSIENT THERMAL IMPEDANCE

