

SAFETY DATA SHEET

According to REACH Regulation (EC) No 1907/2006, as amended by UK REACH Regulations SI 2019/758

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1 Product identifier

Product name: FUCHS MAINTENANCE SPRAY

1.2 Relevant identified uses of the substance or mixture and uses advised against

Identified uses: Lubricant

Uses advised against: No uses advised against identified.

1.3 Details of the supplier of the safety data sheet

Manufacturer / Supplier FUCHS LUBRICANTS (UK) PLC.
New Century Street
ST1 5HU Hanley
Telephone: +44 (0) 1782 203700

Contact Person: Product Safety department
E-mail: product.safety@fuchs.com
Telephone: +44 (0) 1782 203700

1.4 Emergency telephone number: UK NHS: Dial 111

SECTION 2: Hazards identification

Product name: FUCHS MAINTENANCE SPRAY

2.1 Classification of the substance or mixture

The product has been classified and labelled as hazardous according to regulation GB-CLP.

Classification according to GB-CLP.

Physical Hazards

Aerosols	Category 1	H222: Extremely flammable aerosol. H229: Pressurized container: May burst if heated.
----------	------------	---

Health Hazards

Specific Target Organ Toxicity - Single Exposure	Category 3	H336: May cause drowsiness or dizziness.
Specific Target Organ Toxicity - Repeated Exposure	Category 1	H372: Causes damage to organs through prolonged or repeated exposure.
Aspiration Hazard	Category 1	H304: May be fatal if swallowed and enters airways.

Environmental Hazards

Chronic hazards to the aquatic environment	Category 2	H411: Toxic to aquatic life with long lasting effects.
--	------------	--

Hazard summary

Physical Hazards: Flammable aerosol.

Health Hazards

Inhalation: Has a narcotic effect.

Ingestion: If ingested, material may be aspirated into the lungs and cause chemical pneumonitis. Treat appropriately.

2.2 Label Elements

Contains: White Spirit, low viscous



Signal Words: Danger

Hazard Statement(s): H222: Extremely flammable aerosol.
H229: Pressurized container: May burst if heated.
H336: May cause drowsiness or dizziness.
H372: Causes damage to organs through prolonged or repeated exposure by inhalation.
H411: Toxic to aquatic life with long lasting effects.

Product name: FUCHS MAINTENANCE SPRAY

Precautionary Statements

Prevention:	P102: Keep out of reach of children. P210: Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking. P211: Do not spray on an open flame or other ignition source. P251: Do not pierce or burn, even after use. P260: Do not breathe spray. P273: Avoid release to the environment.
Storage:	P410+P412: Protect from sunlight. Do not expose to temperatures exceeding 50 °C/122°F.
Disposal:	P501: Dispose of contents/container to an appropriate treatment and disposal facility in accordance with applicable laws and regulations, and product characteristics at time of disposal.

Supplemental label information

EUH208: Contains: Barium alkyl sulphonate, Barium compounds, Barium alkyl sulphonate. May produce an allergic reaction.

2.3 Other hazards:	By handling of mineral oil products and chemical products no particular hazard is known when normal precautions (item 7) and personal protective equipment (item 8) are kept. The product may not be released into the environment without control.
---------------------------	---

SECTION 3: Composition/information on ingredients

3.2 Mixtures

General information:	Mixture of components with propellant in aerosol can.
-----------------------------	---

Product name: FUCHS MAINTENANCE SPRAY

Chemical name	Identifier	Concentration *	UK-REACH Regis- tration No.	Notes
White Spirit, low viscous	EC: 919-446-0	50,00% - <100,00%		
Butane	EINECS: 203-448-7	0% - <100,00%		
Propane	EINECS: 200-827-9	0% - <100,00%		
Isobutane (<0,1% 1,3-butadiene)	EINECS: 200-857-2	0% - <100,00%		
wax ester	EINECS: 271-626-1	1,00% - <5,00%		
Heterocyclic N-compound	EINECS: 202-414-9	0,25% - <1,00%		
Oleic acid derivative	EINECS: 701-177-3	0,10% - <1,00%		
Fatty alcohol polyglycol ether	EC: 616-609-5	0,10% - <1,00%		
Barium alkyl sulphonate	EINECS: 298-635-3	0,10% - <1,00%		
Barium compounds	EINECS: 263-140-3	0,10% - <1,00%		
Barium alkyl sulphonate	EINECS: 296-719-4	0,10% - <1,00%		

* All concentrations are percent by weight unless ingredient is a gas. Gas concentrations are in percent by volume.

PBT: persistent, bioaccumulative and toxic substance.

vPvB: very persistent and very bioaccumulative substance.

Classification

Chemical name	Identifier	Classification
White Spirit, low viscous	EC: 919-446-0	GBCLP: Asp. Tox. 1;H304, Flam. Liq. 3;H226, STOT SE 3;H336, Aquatic Chronic 2;H411, STOT RE 1;H372
Butane	EINECS: 203-448-7	GBCLP: Flam. Gas 1A;H220, Press. Gas Compr. Gas;H280
Propane	EINECS: 200-827-9	GBCLP: Flam. Gas 1A;H220, Press. Gas Compr. Gas;H280
Isobutane (<0,1% 1,3-butadiene)	EINECS: 200-857-2	GBCLP: Flam. Gas 1A;H220, Press. Gas Compr. Gas;H280
wax ester	EINECS: 271-626-1	GBCLP: Eye Irrit. 2;H319
Heterocyclic N-compound	EINECS: 202-414-9	GBCLP: Skin Corr. 1C;H314, Eye Dam. 1;H318, STOT RE 2;H373, Aquatic Acute 1;H400, Aquatic Chronic 1;H410, Acute Tox. 4;H302; M-Factor (aquatic acute): 10; M-Factor (aquatic chronic): 1
Oleic acid derivative	EINECS: 701-177-3	GBCLP: Eye Dam. 1;H318, Aquatic Acute 1;H400, Skin Irrit. 2;H315, Aquatic Chronic 3;H412, Acute Tox. 4;H332
Fatty alcohol polyglycol ether	EC: 616-609-5	GBCLP: Eye Irrit. 2;H319, Aquatic Chronic 3;H412, Aquatic Acute 1;H400; M-Factor (aquatic acute): 1
Barium alkyl sulphonate	EINECS: 298-635-3	GBCLP: Skin Sens. 1B;H317
Barium compounds	EINECS: 263-140-3	GBCLP: Skin Sens. 1B;H317
Barium alkyl sulphonate	EINECS: 296-719-4	GBCLP: Skin Sens. 1B;H317

GB-CLP

Product name: FUCHS MAINTENANCE SPRAY

specific concentration limit

Chemical name	Identifier	specific concentration limit	Hazard class	Hazard Category	Hazard statements
Barium alkyl sulphonate	EINECS: 298-635-3	> 10 %	Skin sensitizer	1B	H317
Barium compounds	EINECS: 263-140-3	> 10 %	Skin sensitizer	1B	H317
Barium alkyl sulphonate	EINECS: 296-719-4	> 10 %	Skin sensitizer	1B	H317

For the wording of the listed hazard statements refer to section 16.

SECTION 4: First aid measures

General: Instantly remove any clothing soiled by the product.

4.1 Description of first aid measures

Inhalation: Supply fresh air; consult doctor in case of symptoms.

Eye contact: Promptly wash eyes with plenty of water while lifting the eye lids.

Skin Contact: Wash with soap and water.

Ingestion: Call a physician or poison control center immediately. Rinse mouth. Never give liquid to an unconscious person. If vomiting occurs, keep head low so that stomach content doesn't get into the lungs. Do NOT induce vomiting.

4.2 Most important symptoms and effects, both acute and delayed: If ingested, material may be aspirated into the lungs and cause chemical pneumonitis. Treat appropriately. Dizziness Freeze burns

4.3 Indication of any immediate medical attention and special treatment needed Get medical attention if symptoms occur.

SECTION 5: Firefighting measures

5.1 Extinguishing media

Suitable extinguishing media: CO₂, fire extinguishing powder or fog like water spraying. Extinguish larger fires with alcohol resistant foam or spray water with suitable surfactant added

Unsuitable extinguishing media: Water with a full water jet.

5.2 Special hazards arising from the substance or mixture: Danger of explosion with aerosol cans.

5.3 Advice for firefighters

Product name: FUCHS MAINTENANCE SPRAY

Special fire-fighting procedures:	Move container from fire area if it can be done without risk. Dispose of fire debris and contaminated fire fighting water in accordance with official regulations. Collect contaminated fire fighting water separately. It must not enter drains.
Special protective equipment for fire-fighters:	Self-contained breathing apparatus and full protective clothing must be worn in case of fire.

SECTION 6: Accidental release measures

6.1 Personal precautions, protective equipment and emergency procedures:	Not required.
6.2 Environmental Precautions:	Avoid release to the environment. Prevent further leakage or spillage if safe to do so.
6.3 Methods and material for containment and cleaning up:	Scrape up spillage or absorb with absorbing material. Stop the flow of material, if this is without risk. Dispose of the material collected according to regulations.
6.4 Reference to other sections:	See Section 8 of the SDS for Personal Protective Equipment. See Section 7 for information on safe handling See Section 13 for information on disposal.

SECTION 7: Handling and storage:

7.1 Precautions for safe handling:	Avoid contact with flame and heat source, prevent contact with direct sunlight Use only in well-ventilated areas.
7.2 Conditions for safe storage, including any incompatibilities:	Store locked up. Local regulations concerning handling and storage of waterpolluting products have to be followed. Local regulations for the storage and handling of aerosol cans and flammable liquids have to be kept. Keep away from heat/sparks/hot surfaces. - No smoking.
7.3 Specific end use(s):	Not applicable
Storage Class:	2 B, Aerosols

SECTION 8: Exposure controls/personal protection

8.1 Control Parameters

Occupational Exposure Limits

Chemical name	Type	Exposure Limit Values	Source
Butane	TWA	600 ppm 1.450 mg/m3	UK. EH40 Workplace Exposure Limits (WELs), as amended (12 2011)
Butane	STEL	750 ppm 1.810 mg/m3	UK. EH40 Workplace Exposure Limits (WELs), as amended (12 2011)

8.2 Exposure controls

Product name: FUCHS MAINTENANCE SPRAY

Appropriate engineering controls:

Provide adequate ventilation. Ventilation rates should be matched to conditions. If applicable, use process enclosures, local exhaust ventilation, or other engineering controls to maintain airborne levels below recommended exposure limits. If exposure limits have not been established, maintain airborne levels to an acceptable level.

Individual protection measures, such as personal protective equipment

General information:

Wash hands before breaks and after work. Use personal protective equipment as required. Personal protection equipment should be chosen according to the CEN standards and in discussion with the supplier of the personal protective equipment. The usual precautionary measures should be adhered to in handling the chemicals or the mineral oil products.

Eye/face protection:

Safety glasses (EN 166) recommended during refilling. Avoid contact with skin and eyes. Goggles/face shield are recommended. If risk of splashing, wear safety goggles or face shield.

Skin protection

Hand Protection:

Material: Nitrile butyl rubber (NBR).
Min. Breakthrough time: ≥ 480 min
Recommended thickness of the material: $\geq 0,38$ mm

Avoid long-term and repeated skin contact. Suitable gloves can be recommended by the glove supplier. Use skin protection cream for preventive skin protection. Protective gloves, where permitted in acc. to safety directions. The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.

Other:

Do not carry cleaning cloths impregnated with the product in trouser pockets. Wear suitable protective clothing.

Respiratory Protection:

Ensure good ventilation/exhaustion at the workplace. Avoid breathing vapour/ aerosol.

Thermal hazards:

Not known.

Hygiene measures:

Always observe good personal hygiene measures, such as washing after handling the material and before eating, drinking, and/or smoking. Routinely wash work clothing to remove contaminants. Discard contaminated footwear that cannot be cleaned.

Environmental Controls:

No data available.

SECTION 9: Physical and chemical properties

9.1 Information on basic physical and chemical properties

Appearance

Physical state:	Aerosols
Form:	Aerosols
Color:	Pale yellow

Product name: FUCHS MAINTENANCE SPRAY

Odor:	Characteristic
pH:	substance/mixture is non-soluble (in water)
Freezing point:	not determined
Boiling Point:	not determined
Flash Point:	Value not relevant for classification
Evaporation Rate:	Not applicable for mixtures
Flammability (solid, gas):	not determined
Flammability Limit - Upper (%)—:	Not applicable for mixtures
Flammability Limit - Lower (%)—:	Not applicable for mixtures
Vapor pressure:	Not applicable for mixtures
Relative vapor density:	Not applicable for mixtures
Density:	0,69 g/cm ³ (15 °C)
Solubility(ies)	
Solubility in Water:	Insoluble in water
Solubility (other):	No data available.
Partition coefficient (n-octanol/water):	Not applicable for mixtures
Autoignition Temperature:	not determined
Decomposition Temperature:	not determined
Flow time	Value not relevant for classification
Explosive properties:	Value not relevant for classification
Oxidizing properties:	Value not relevant for classification
Particle characteristics:	Not applicable
9.2 Other information	No data available.

SECTION 10: Stability and reactivity

10.1 Reactivity:	Stable under normal use conditions.
10.2 Chemical Stability:	Stable under normal use conditions.
10.3 Possibility of hazardous reactions:	Stable under normal use conditions.
10.4 Conditions to avoid:	Stable under normal use conditions.
10.5 Incompatible Materials:	Strong oxidizing substances. Strong acids. Strong bases.
10.6 Hazardous Decomposition Products:	Thermal decomposition or combustion may liberate carbon oxides and other toxic gases or vapors.

Product name: FUCHS MAINTENANCE SPRAY

SECTION 11: Toxicological information

11.1 Information on toxicological effects

Acute toxicity

Oral

Product: Not classified for acute toxicity based on available data.

Specified substance(s)

White Spirit, low viscous LD 50 (Rat): > 15.000 mg/kg

Heterocyclic N-compound LD 50 (Rat): 1.265 mg/kg (OECD 401)

Oleic acid derivative LD 50 (Rat): > 5.000 mg/kg

Dermal

Product: Not classified for acute toxicity based on available data.

Inhalation

Product: Not classified for acute toxicity based on available data.

Specified substance(s)

White Spirit, low viscous LC 50 (Rat, 4 h): > 13,1 mg/l

Butane LC 50 (Rat, 4 h): 658 mg/l
Gas

Oleic acid derivative LC 50 (Rat, 4 h): 1,37 mg/l

Skin Corrosion/Irritation:

Product: Based on available data, the classification criteria are not met.

Specified substance(s)

Heterocyclic N-compound OECD 404 (Rabbit):
Corrosive.

Serious Eye Damage/Eye Irritation:

Product: Based on available data, the classification criteria are not met.

Specified substance(s)

wax ester
Causes serious eye irritation.

Heterocyclic N-compound OECD 405 (Rabbit):
Corrosive.

Respiratory or Skin Sensitization:

Product: Skin sensitizer: Based on available data, the classification criteria are not met.
Respiratory sensitizer: Based on available data, the classification criteria are not met.

Specified substance(s)

Heterocyclic N-compound
No sensitizing effect (guinea pig); OECD 406

Product name: FUCHS MAINTENANCE SPRAY

Germ Cell Mutagenicity

Product: Based on available data, the classification criteria are not met.

Carcinogenicity

Product: Based on available data, the classification criteria are not met.

Reproductive toxicity

Product: Based on available data, the classification criteria are not met.

Specific Target Organ Toxicity - Single Exposure

Product: Based on available data, the classification criteria are met.

Specific Target Organ Toxicity - Repeated Exposure

Product: Based on available data, the classification criteria are met.

Aspiration Hazard

Product: May be fatal if swallowed and enters airways.

Other adverse effects: No data available.

SECTION 12: Ecological information

12.1 Toxicity**Acute toxicity**

Product: Based on available data, the classification criteria are not met.

Fish**Specified substance(s)**

White Spirit, low viscous LC 50 (Fish, 96 h): 10 - 30 mg/l

Propane LC 50 (Fish, 96 h): > 1.000 mg/l

Isobutane (<0,1% 1,3-butadiene) LC 50 (Fish, 96 h): 28 mg/l

Heterocyclic N-compound LC 50 (Fish, 96 h): 0,3 mg/l (OECD 203)

Oleic acid derivative LC 50 (Fish, 96 h): 6,8 mg/l

Aquatic Invertebrates**Specified substance(s)**

White Spirit, low viscous EC 50 (Water Flea, 48 h): 10 - 20 mg/l (OECD 202)

Isobutane (<0,1% 1,3-butadiene) EC 50 (Water Flea, 48 h): 16,3 mg/l

Heterocyclic N-compound EC 50 (Water Flea, 48 h): 0,136 mg/l (OECD 202)

Oleic acid derivative EC 50 (Water Flea, 48 h): 0,43 mg/l

Chronic Toxicity

Product name: FUCHS MAINTENANCE SPRAY

Product: Based on available data, the classification criteria are met.

Toxicity to Aquatic Plants

Specified substance(s)

White Spirit, low viscous EC 50 (Alga, 72 h): 4,6 - 10 mg/l (OECD 201)

Isobutane (<0,1% 1,3-butadiene) EC 50 (Alga, 72 h): 8,6 mg/l

Heterocyclic N-compound EC 50 (Alga, 72 h): 0,03 mg/l (OECD 201)
NOEC (Alga, 72 h): 0,11 mg/l

Oleic acid derivative EC 50 (Alga, 72 h): 6,3 mg/l
NOEC (Alga, 72 h): 0,91 mg/l

12.2 Persistence and Degradability

Biodegradation

Product: Not applicable for mixtures

Specified substance(s)

Heterocyclic N-compound (OECD 301B) The product is not biodegradable.

12.3 Bioaccumulative potential

Product: Not applicable for mixtures

12.4 Mobility in soil:

Product: Not applicable for mixtures

12.5 Results of PBT and vPvB assessment:

The product does not contain any substances fulfilling the PBT/vPvB criteria.

12.6 Other adverse effects:

Toxic to aquatic life with long lasting effects.

Water Hazard Class (WGK):

WGK 3: severely water-endangering.

SECTION 13: Disposal considerations
--

13.1 Waste treatment methods

General information: Dispose in accordance with all applicable regulations.

Disposal methods: Discharge, treatment, or disposal may be subject to national, state, or local laws.

List of Waste (LoW) Codes

16 05 04*: Gases in pressure containers (including halons) containing hazardous substances.

Product name: FUCHS MAINTENANCE SPRAY

SECTION 14: Transport information

ADR/RID

14.1 UN number or ID number:	UN 1950
14.2 UN Proper Shipping Name:	AEROSOLS
14.3 Transport Hazard Class(es)	
Class:	2
Label(s):	2.1
Hazard No. (ADR):	–
Tunnel restriction code:	(D)
14.4 Packing Group:	–
14.5 Environmental hazards:	–
14.6 Special precautions for user:	–

IMDG

14.1 UN number or ID number:	UN 1950
14.2 UN Proper Shipping Name:	AEROSOLS
14.3 Transport Hazard Class(es)	
Class:	2.1
Label(s):	2.1
EmS No.:	F-D, S-U
14.3 Packing Group:	–
14.5 Environmental hazards:	–
14.6 Special precautions for user:	–

IATA

14.1 UN number or ID number:	UN 1950
14.2 Proper Shipping Name:	Aerosols, flammable
14.3 Transport Hazard Class(es):	
Class:	2.1
Label(s):	2.1
14.4 Packing Group:	–
14.5 Environmental hazards:	–
14.6 Special precautions for user:	–

14.7 Transport in bulk according to Annex II of MARPOL and the IBC Code: Not applicable.

SECTION 15: Regulatory information

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture:

GB Regulations

The Ozone-Depleting Substances and Fluorinated Greenhouse Gases (Amendment etc.) (EU Exit) Regulations 2019:
none

The Persistent Organic Pollutants (Amendment) (EU Exit) Regulations 2020:
none

Product name: FUCHS MAINTENANCE SPRAY

15.2 Chemical safety assessment:

No Chemical Safety Assessment has been carried out.

DIRECTIVE Control of Major Accident Hazards Regulations 2015:

The product falls into the scope of the Control of Major Accident Hazards Regulations 2015.

Hazard category in accordance with GB-CLP	Qualifying quantity for the application of Lower-tier requirements:	Qualifying quantity for the application of Upper-tier requirements:
P3a: P3a. Flammable aerosols	150 t	500 t
E2: E2. Hazardous to the aquatic environment	200 t	500 t

SECTION 16: Other information

Revision Information:

Vertical lines in the margin indicate an amendment.

Wording of the H-statements in section 2 and 3

H220	Extremely flammable gas.
H222	Extremely flammable aerosol.
H226	Flammable liquid and vapor.
H229	Pressurized container: May burst if heated.
H280	Contains gas under pressure; may explode if heated.
H302	Harmful if swallowed.
H304	May be fatal if swallowed and enters airways.
H314	Causes severe skin burns and eye damage.
H315	Causes skin irritation.
H317	May cause an allergic skin reaction.
H318	Causes serious eye damage.
H319	Causes serious eye irritation.
H332	Harmful if inhaled.
H336	May cause drowsiness or dizziness.
H372	Causes damage to organs through prolonged or repeated exposure by inhalation.
H373	May cause damage to organs through prolonged or repeated exposure.
H400	Very toxic to aquatic life.
H410	Very toxic to aquatic life with long lasting effects.
H411	Toxic to aquatic life with long lasting effects.
H412	Harmful to aquatic life with long lasting effects.

Other information:

The classification complies with the current GB lists; however, it has been supplemented with expert literature information and information provided by/about our company. The following evaluation methods were used: On the basis of test data; Calculation Method; Bridging Principle "Substantially similar mixtures"; Expert Judgement

Revision Date:

10.01.2023

Product name: FUCHS MAINTENANCE SPRAY

Disclaimer:

The data contained in this safety data sheet are based on our current knowledge and experience and are given to the best of our knowledge and belief. It characterizes the product only with regard to safety requirements for handling, transport and disposal. The data do not describe the product's properties (tech. product specification). Neither should any agreed property nor the suitability of the product for any specific technical application be deduced from the data contained in this safety data sheet. Modifications on this document are not allowed. The data are not transferable to other products. In the case of mixing the product with other products or in the case of processing, the data in this safety data sheet are not necessarily valid for the new-made material. It is the responsibility of the recipient of the product to observe federal, state and local law. Please contact us to obtain up-to-date safety data sheets. This document was issued electronically and has no signature.