




PIDG

TE Internal #: 160170
Spade Tongue Terminal, 16 – 14 AWG, M5 Stud, 5.2 mm [.205 in]
Stud Diameter, Closed Barrel, Straight, Tin Plating, Partially
Insulated, PIDG

[View on TE.com >](#)

Terminals & Splices > Spade Terminals



Spade Terminal Type: **Spade Tongue Terminal**
Wire Size: **2050 – 5180 CMA**
Stud Size: **M5**

Features

Product Type Features

Stud Size	M5
Sealable	No
Wire Insulation Support Retention Type	Insulation Support

Configuration Features

Number of Holes	1
-----------------	---

Electrical Characteristics

Voltage Rating	300 V
----------------	-------

Body Features

Product Weight	1.087 g
Insulation Sleeve Color	Blue
Stripe Color	Blue

Contact Features

Spade Terminal Type	Spade Tongue Terminal
Barrel Type	Closed
Terminal Orientation	Straight



Terminal Plating Material	Tin
---------------------------	-----

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Dimensions

Wire Size	2050 – 5180 CMA
Stud Diameter	5.2 mm[.205 in]
Tongue Thickness	.79 mm[.031 in]
Product Length	23.4 mm[.921 in]
Compatible Insulation Diameter (Max)	4.32 mm[.17 in]
Compatible Insulation Diameter Range	2.92 – 4.31 mm[.115 – .17 in]

Usage Conditions

Insulation Option	Partially Insulated
-------------------	---------------------

Operation/Application

Compatible With Wire Base Material	Copper
Compatible With Wire Plating Material	Tin

Industry Standards

Government Qualified Terminal	No
-------------------------------	----

Packaging Features

Packaging Quantity	1000
Packaging Method	Loose Piece

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free



Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 2392022-1 BLUE BATTERY DAHT KIT 110V (47387-7)	TE Part # 169404 CERTI-LOK DIE	TE Part # 47387-7 DAHT PG PIDG 16-12 ASSY	TE Part # 2392022-2 BLUE BATTERY DAHT KIT 220V (47387-7)
TE Part # 169400 CERTI-LOK FRAME W/O DIES	TE Part # 47387 DAHT PG PIDG 20-14 ASSY	TE Part # 58423-1 DIE, RBY IS9252	TE Part # 58433-3 PRO CR ASSY, RBY IS9252
TE Part # 525691 DAHT PG PIDG 16-14 ASSY	TE Part # 59824-1 TETRA-CRIMP PIDG PG FASTON 22-10 ASSY		

Also in the Series | PIDG



Compression Connectors(17)



Crimp Wire Pins, Tabs & Ferrules(41)



Knife Disconnects(11)



Quick Disconnects(38)



Ring Terminals(588)



Spade Terminals(228)



Special Purpose Terminals(1)



Splices(41)

Customers Also Bought

TE Part #3363736003
LSTT-R-6.4-0

TE Part #650934-5
064 EURO TYPE R PIN ST ASSY

TE Part #345212-1
070 SERIES TAB

TE Part #3-1879642-6
H8 250R 0.1% 25PPM

TE Part #354868-E
STVD 32 M AC GG 4-00 1006 ** 247 E 172

TE Part #826467-8
8P MOD II SHROUDED HEADER, ST

TE Part #324123
PIDG R 22-16COMM 22-18MIL 5/16

TE Part #826467-4
4P MOD II SHROUDED HEADER, ST

TE Part #826469-8
2X8P MOD II SHROUDED HEADER, ST

TE Part #826467-5
5P MOD II SHROUDED HEADER, ST

Documents



Product Drawings

TERM, SPADE, PIDG, 16-14, M5

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_160170_F.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_160170_F.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_160170_F.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Agency Approvals

CSA Certificate

English