


## FEATURES

- **High hardness (Shore A 90 to 95):** Provides excellent resistance to deformation and wear
- **Wide temperature range (-20 °C to 140 °C):** Suitable for diverse environmental conditions
- **Large inside diameter (608.1 mm):** Accommodates various fitting requirements
- **Durable materials:** Fluorinated Ethylene Propylene, Fluoroelastomer, and Viton ensure chemical resistance and longevity
- **Compliant with multiple standards:** Meets BS ISO 3601-1, AS 568, and more for assured quality

## RS PRO Black O-Ring Seal, Shore A 90 to 95

RS Stock No: 731-643



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

This RS PRO O-Ring Seal is designed for reliable sealing in a variety of industrial applications. Made from high-quality materials such as Fluorinated Ethylene Propylene, Fluoroelastomer, and Viton, it offers excellent resistance to chemicals and high temperatures, ensuring durability and performance. Ideal for use in environments requiring robust sealing solutions.

## General Specifications

Colour	Black
Hardness	Shore A 90 to 95
Product Type	O-Ring Seal
Sub Type	O-Ring

## Mechanical Specifications

Inside Diameter	608.1 mm
Material	Fluorinated Ethylene Propylene, Fluoroelastomer, Viton
Outside Diameter	622.08 mm
Thickness	6.99 mm

## Operation Environment Specifications

Maximum Operating Temperature	140 °C
Minimum Operating Temperature	-20 °C

## Approvals

Standards/Approvals	BS ISO 3601-1, AS 568, EC 1935:2004, FDA, ISO 14001:2015, ISO 45001:2015, ISO 9001:2015, LABS, TSCA, USP Class VI, WRAS
---------------------	---

