



Safety Data Sheet according to (EC) No 1907/2006 - ISO 11014-1

Page 1 of 6

TEROSTAT PU 92 GREY 310ML

sds no. : 180799
V004.0

Revision: 28.04.2010
printing date: 21.05.2010

CP1142 v1.2 RS 630-1028

RS REACH revision date 01/06/10

1. Identification of the substance/preparation and of the company/undertaking

Trade name:

TEROSTAT PU 92 GREY 310ML

Intended use:

adhesive and sealant

Company name:

Henkel Limited
Technologies House
Wood Lane End
HP2 4RQ Hemel Hempstead

Great Britain

Phone: +44 (0)1442 278000

Fax-no.: +44 (0)1442 278071

E-mail address of person responsible for Safety Data Sheet:

ua-productsafety.uk@uk.henkel.com

Emergency information:

24 Hours Emergency Tel: +44 (0)1442 278497

Supplied by:

RS Components Ltd,
Birchington Road, Corby, Northants, NN17 9RS.
Tel: +44 (0) 1536 402888 (8am to 8pm)
Email: technical.help@rs-components.com

2. Hazards identification

The product is classified as hazardous within the meaning of the valid (EU) preparation directive.

Xn - Harmful

R42 May cause sensitization by inhalation.

Persons suffering from allergic reactions to isocyanates should avoid contact with the product.

3. Composition / information on ingredients

General chemical description:

Sealant

Base substances of preparation:

Polyurethane prepolymer with free 4,4'-methylenediphenyl diisocyanate (MDI)

Declaration of ingredients according to (EC) No 1907/2006:

Hazardous components CAS-No.	EINECS ELINCS	content	Classification
Xylene - mixture of isomeres 1330-20-7	215-535-7	< 5 %	Xn - Harmful; R20/21 Xi - Irritant; R38 R10
Alkanes, C9-12-iso- 90622-57-4	292-459-0	< 2 %	Xn - Harmful; R65, R66 R53
4,4'- methylenediphenyl diisocyanate 101-68-8	202-966-0	< 1 %	Xn - Harmful; R20 Xi - Irritant; R36/37/38 R42/43
Methylenediphenyl diisocyanate 26447-40-5	247-714-0	< 1 %	Xn - Harmful; R20 Xi - Irritant; R36/37/38 R42/43

For full text of the R-Phrases indicated by codes see section 16 'Other Information'.

Substances without classification may have community workplace exposure limits available.

4. First aid measures

Inhalation:

Fresh air, oxygen supply, warmth; seek specialist medical attention.

Skin contact:

Rinse with running water and soap. Apply replenishing cream. Change all contaminated clothing.

Eye contact:

Rinse immediately with plenty of running water (for 10 minutes). Seek medical attention if necessary.

Ingestion:

Rinse mouth, drink 1-2 glasses of water, do not induce vomiting, consult a doctor.

5. Fire fighting measures

Suitable extinguishing media:

All common extinguishing agents are suitable.

Extinguishing media which must not be used for safety reasons:

Water jet (solvent-containing product).

Special protection equipment for firefighters:

Wear protective equipment.

Wear self-contained breathing apparatus.

Hazardous combustion products:

Isocyanate vapors, carbon oxides.

6. Accidental release measures

Personal precautions:

Wear protective equipment.

Avoid contact with skin and eyes.

Don't breathe vapours or aerosole.

See advice in chapter 8

Environmental precautions:

Do not empty into drains / surface water / ground water.

Clean-up methods:

Remove mechanically.

Dispose of contaminated material as waste according to item 13.

7. Handling and storage

Handling:

Avoid open flames and sources of ignition.
Take measures to prevent the build-up of electrostatic charges.

Storage:

Store in sealed original container protected against moisture.
Ensure good ventilation/extraction.
Store in a cool, dry place.
Container must be made airtight after use.
Storage at 15 to 25°C is recommended.

8. Exposure controls / personal protection

Components with specific control parameters for workplace:

Valid for

Great Britain

Basis

UK EH40 WELs

Ingredient	ppm	mg/m3	Type	Category	Remarks
XYLENE, MIXED ISOMERS, PURE 1330-20-7	50	221	Time Weighted Average (TWA).		ECLTV
XYLENE, MIXED ISOMERS, PURE 1330-20-7	100	442	Short Term Exposure Limit (STEL):		ECLTV
XYLENE, MIXED ISOMERS, PURE 1330-20-7			Skin designation:	Can be absorbed through the skin.	ECLTV
XYLENE, O-, M-, P- OR MIXED ISOMERS 1330-20-7	50	220	Time Weighted Average (TWA).		EH40 WEL
XYLENE, O-, M-, P- OR MIXED ISOMERS 1330-20-7	100	441	Short Term Exposure Limit (STEL):		EH40 WEL
XYLENE, O-, M-, P- OR MIXED ISOMERS 1330-20-7			Skin designation:	Can be absorbed through the skin.	EH40 WEL
ISOCYANATES, ALL (AS -NCO) 101-68-8		0,07	Short Term Exposure Limit (STEL):		EH40 WEL
ISOCYANATES, ALL (AS -NCO) 101-68-8		0,02	Time Weighted Average (TWA).		EH40 WEL

Engineering controls:

Ensure good ventilation/extraction.

Respiratory protection:

Suitable breathing mask when there is inadequate ventilation.

Hand protection:

Chemical-resistant protective gloves (EN 374). Suitable materials for short-term contact or splashes (recommended: at least protection index 2, corresponding to > 30 minutes permeation time as per EN 374): Fluorinated rubber (FKM; >= 0.7 mm thickness) Suitable materials for longer, direct contact (recommended: protection index 6, corresponding to > 480 minutes permeation time as per EN 374): Fluorinated rubber (FKM; >= 0.7 mm thickness) This information is based on literature references and on information provided by glove manufacturers, or is derived by analogy with similar substances. Please note that in practice the working life of chemical-resistant protective gloves may be considerably shorter than the permeation time determined in accordance with EN 374 as a result of the many influencing factors (e.g. temperature). If signs of wear and tear are noticed then the gloves should be replaced.

Eye protection:

Goggles which can be tightly sealed.

Skin protection:

Wear protective equipment.
Protective clothing that covers arms and legs.

General protection and hygiene measures:

Do not eat, drink or smoke while working.

Wash hands before work breaks and after finishing work.

Use only personal protection that's CE-labelled according to the regulation no. 819 of 19 August 1994.

9. Physical and chemical properties**General characteristics:**

Appearance	Paste pasty Grey
Odor:	of solvent

Phys./chem. properties:

Flash point	not applicable
Vapor pressure (20 °C (68 °F))	< 100 mbar
Density (20 °C (68 °F))	1,19 g/cm ³
Solubility (qualitative) (20 °C (68 °F); Solvent: Water)	Insoluble
Explosion limit lower [vol%]	0,1 % (V)
upper [vol%]	7,6 % (V)
Ignition temperature	> 200 °C (> 392 °F)
VOC content (VOCV 814.018 VOC regulation CH)	5,9 %

10. Stability and reactivity**Conditions to avoid:**

No decomposition if used according to specifications.

Materials to avoid:

None if used for intended purpose.

Hazardous decomposition products:

At higher temperatures isocyanate may be released.

No decomposition if used according to specifications.

11. Toxicological information**General toxicological information:**

The present product is a chemical preparation within the meaning of the chemicals act. The following evaluation has been made on the basis of the toxicological data and content by weight of the individual ingredients.

Persons suffering from allergic reactions to isocyanates should avoid contact with the product.

Sensitizing:

May cause sensitization by inhalation.

12. Ecological information**General ecological information:**

Do not empty into drains, soil or bodies of water.

13. Disposal considerations**Product disposal:**

The valid EEC waste code numbers are not product-related but are largely source-related. These can be requested from the manufacturer.

In consultation with the responsible local authority, must be subjected to special treatment.

14. Transport information**General information:**

Not hazardous according to RID, ADR, ADNR, IMDG, IATA-DGR.

15. Regulations - classification and identification**Indication of danger:**

Xn - Harmful

**Contains**

4,4'-methylenediphenyl diisocyanate,
Methylenediphenyl diisocyanate

Risk phrases:

R42 May cause sensitization by inhalation.

Safety phrases:

S23 Do not breathe vapour.
S28 After contact with skin, wash immediately with plenty of water and soap.
S36/37/39 Wear suitable protective clothing, gloves and eye/face protection.
S45 In case of accident or if you feel unwell, seek medical advice immediately (show the label where possible).

Additional labeling:

Contains isocyanates. See information supplied by the manufacturer.

VOC Paints and Varnishes (EU):

Product (sub)category:

This product is not a subject of the Directive 2004/42/EC

16. Other information

The labelling of the product is indicated in Section 15. The full text of the R-phrases indicated by codes in this safety data sheet are as follows:

- R10 Flammable.
- R20 Harmful by inhalation.
- R20/21 Harmful by inhalation and in contact with skin.
- R36/37/38 Irritating to eyes, respiratory system and skin.
- R38 Irritating to skin.
- R42/43 May cause sensitization by inhalation and skin contact.
- R53 May cause long-term adverse effects in the aquatic environment.
- R65 Harmful: may cause lung damage if swallowed.
- R66 Repeated exposure may cause skin dryness or cracking.

Further information:

This information is based on our current level of knowledge and relates to the product in the state in which it is delivered. It is intended to describe our products from the point of view of safety requirements and is not intended to guarantee any particular properties.