

4

3

2

1

© 2019 TE Connectivity. All Rights Reserved.

2371404-2	1.25	6.0	6.50	1.25	6.15	2	A	NATURAL	2360540-2	-	
2371404-3	2.50	6.0	7.75	2.50	7.40	3			2360540-3		
2371404-4	3.75	6.0	9.00	3.75	8.65	4			2360540-4		
2371404-5	5.00	6.0	10.25	5.00	9.90	5			2360540-5		
2371404-6	6.25	6.0	11.50	6.25	11.15	6			2360540-6		
2371404-7	7.50	6.0	12.75	7.50	12.40	7			2360540-7		
2371404-8	8.75	8.8	14.00	8.75	13.65	8			2360540-8		
2371404-9	10.00	8.8	15.25	10.00	14.90	9			2360540-9		
1-2371404-0	11.25	8.8	16.50	11.25	16.15	10			1-2360540-0		
1-2371404-1	12.50	8.8	17.75	12.50	17.40	11			1-2360540-1		
1-2371404-2	13.75	8.8	19.00	13.75	18.65	12			1-2360540-2		
1-2371404-3	15.00	8.8	20.25	15.00	19.90	13			1-2360540-3		
1-2371404-4	16.25	8.8	21.50	16.25	21.15	14			1-2360540-4		
1-2371404-5	17.50	8.8	22.75	17.50	22.40	15			1-2360540-5		
1-2371404-6	18.75	8.8	24.00	18.75	23.65	16			1-2360540-6		
1-2371404-7	20.00	8.8	25.25	20.00	24.90	17			1-2360540-7		
1-2371404-8	21.25	8.8	26.50	21.25	26.15	18			1-2360540-8		
2-2371404-2	1.25	6.0	6.50	1.25	6.15	2			2-2360540-2		B
2-2371404-3	2.50	6.0	7.75	2.50	7.40	3	2-2360540-3				
2-2371404-4	3.75	6.0	9.00	3.75	8.65	4	2-2360540-4				
2-2371404-5	5.00	6.0	10.25	5.00	9.90	5	2-2360540-5				
2-2371404-6	6.25	6.0	11.50	6.25	11.15	6	2-2360540-6				
2-2371404-7	7.50	6.0	12.75	7.50	12.40	7	2-2360540-7				
2-2371404-8	8.75	8.8	14.00	8.75	13.65	8	2-2360540-8				
2-2371404-9	10.00	8.8	15.25	10.00	14.90	9	2-2360540-9				
3-2371404-0	11.25	8.8	16.50	11.25	16.15	10	3-2360540-0				
3-2371404-1	12.50	8.8	17.75	12.50	17.40	11	3-2360540-1				
3-2371404-2	13.75	8.8	19.00	13.75	18.65	12	3-2360540-2				
3-2371404-3	15.00	8.8	20.25	15.00	19.90	13	3-2360540-3				
3-2371404-4	16.25	8.8	21.50	16.25	21.15	14	3-2360540-4				
3-2371404-5	17.50	8.8	22.75	17.50	22.40	15	3-2360540-5				
3-2371404-6	18.75	8.8	24.00	18.75	23.65	16	3-2360540-6				
3-2371404-7	20.00	8.8	25.25	20.00	24.90	17	3-2360540-7				
3-2371404-8	21.25	8.8	26.50	21.25	26.15	18	3-2360540-8				
4-2371404-2	1.25	6.0	6.50	1.25	6.15	2	4-2360540-2	C	RED	4-2360540-2	
4-2371404-3	2.50	6.0	7.75	2.50	7.40	3	4-2360540-3				
4-2371404-4	3.75	6.0	9.00	3.75	8.65	4	4-2360540-4				
4-2371404-5	5.00	6.0	10.25	5.00	9.90	5	4-2360540-5				
4-2371404-6	6.25	6.0	11.50	6.25	11.15	6	4-2360540-6				
4-2371404-7	7.50	6.0	12.75	7.50	12.40	7	4-2360540-7			4	
4-2371404-8	8.75	8.8	14.00	8.75	13.65	8	4-2360540-8				
4-2371404-9	10.00	8.8	15.25	10.00	14.90	9	4-2360540-9				
5-2371404-0	11.25	8.8	16.50	11.25	16.15	10	5-2360540-0				
5-2371404-1	12.50	8.8	17.75	12.50	17.40	11	5-2360540-1				
5-2371404-2	13.75	8.8	19.00	13.75	18.65	12	5-2360540-2				
5-2371404-3	15.00	8.8	20.25	15.00	19.90	13	5-2360540-3				
5-2371404-4	16.25	8.8	21.50	16.25	21.15	14	5-2360540-4				
5-2371404-5	17.50	8.8	22.75	17.50	22.40	15	5-2360540-5				
5-2371404-6	18.75	8.8	24.00	18.75	23.65	16	5-2360540-6				
5-2371404-7	20.00	8.8	25.25	20.00	24.90	17	5-2360540-7				
5-2371404-8	21.25	8.8	26.50	21.25	26.15	18	5-2360540-8				
MATING PLUG HOUSING CRIMP VERSION	DIM E	DIM D	DIM C	DIM B	DIM A	POS	KEYING				COLOR

1

MATERIAL
HOUSING: HIGH TEMP NYLON (PA4T), UL94 V-0
POST CONTACT: BRASS, THICKNESS 0.30
METAL PEG: STEEL, THICKNESS 0.25

2

PLATING
POST CONTACT: 1.0um MIN TIN OVER 1.27um MIN NICKEL
METAL PEG: 2.0um MIN TIN OVER 1.27um MIN NICKEL

3

MATING PARTS: SEE TABLE ON PAGE 2.

4

PRELIMINARY: NOT RELEASED FOR PRODUCTION
THIS PRODUCT HAS NOT COMPLETED QUALIFICATION TESTING.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±0.25
2 PLC ±0.15
3 PLC ±
4 PLC ±
ANGLES ±
FINISH

2

DWN R. SMITH 12SEP2019
CHK L. CHEN 12SEP2019
APVD L. CHEN 12SEP219
PRODUCT SPEC 108-106451
APPLICATION SPEC 114-106457
WEIGHT -
CUSTOMER DRAWING

12SEP2019
12SEP2019
12SEP219

NAME
HEADER ASSY, VERTICAL
SG1 1.25, SMT TYPE

SIZE
A2

CAGE CODE
00779

DRAWING NO
C-2360540

RESTRICTED TO
-

SCALE 5:1
SHEET 2 OF 4
REV C

TE Connectivity

TE

1471-9 (3/13)

4

3

2

1

© 2019 TE Connectivity. All Rights Reserved.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

KEY A SHOWN FOR ALL POSITIONS

2 POSITION

3 POSITION

4 POSITION

5 POSITION

6 POSITION

7 POSITION

8 POSITION

9 POSITION

10 POSITION

11 POSITION

12 POSITION

13 POSITION

14 POSITION

15 POSITION

16 POSITION

17 POSITION

18 POSITION

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL

TOLERANCES, UNLESS OTHERWISE SPECIFIED:

0 PLC ±-

1 PLC ±0.25

2 PLC ±0.15

3 PLC ±

4 PLC ±

ANGLES ±

FINISH ±

DWN R. SMITH 12SEP2019

CHK L. CHEN 12SEP2019

APVD L. CHEN 12SEP219

PRODUCT SPEC 108-106451

APPLICATION SPEC 114-106457

WEIGHT -

CUSTOMER DRAWING

NAME HEADER ASSY, VERTICAL
SG1 1.25, SMT TYPE

SIZE A2

CAGE CODE 00779

DRAWING NO C-2360540

RESTRICTED TO -

SCALE 5:1

SHEET 3 OF 4

REV C

TE Connectivity

1471-9 (3/13)

A

1471-9 (3/13)