

**Fuse-link, medium voltage, 6.3 A, AC 17.5 kV, 2", 51 x 442 mm, back-up,
DIN, with striker**



17.5TDMEJ6.3

Product name	Eaton Busmann series medium voltage DIN fuse
Part no.	17.5TDMEJ6.3
EAN	5027590245920
Product Length/Depth	442 millimetre
Product height	53.5 millimetre
Product width	51 millimetre
Product weight	2500 gram
Compliances	DIN 43625 VDE 0670-4 IEC 60282-1
Certifications	IEC60282-1
Product Tradename	None
Product Type	Medium voltage DIN fuse
Product Sub Type	None
Amperage Rating	6.3 A
Voltage rating	17.5 kV
Breaking capacity	50 kA
Performance Cat According To IEC 60282-1	Back-up
Rated frequency - min	50 Hz
Class	Class back-up
Resistance	324 Ohms
Application	transformer protection indoor or outdoor use
Fuse indicator	With Striker
Fuse size	51 x 442 mm
Standard	DIN
Mounting method	Clip-in
Used with	270303 Fuse clip A3354710 Fuse clip

Technical data ETIM 8.0

Circuit breakers and fuses (EG000020) / Medium-/high voltage fuse (EC003507)		
Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse systems / Safety fuse systems (unspecified) (ecl@ss10.0.1-27-14-21-90 [BAB265011])		
Rated current	A	6.3
Rated voltage	kV	17.5
Voltage type		AC
Rated frequency	Hz	50 - 50
Breaking capacity	kA	50
Utilization category		Other
Application		Primary side transformer protection
Length	mm	442
Diameter	mm	51
Performance category according to IEC 60282-1		Back-up
With striker		Yes
Standard		DIN
Release characteristic		Other

