Technical sheet


BTC60POR


Modular barrier Ø 60 mm - swing gate


Modular warehouse barrier designed to ensure safety in industrial areas. It helps to organise vehicle traffic and demarcate high-risk zones, whilst ensuring the protection of people. Made from galvanised steel and coated with yellow epoxy paint. These various components allow for the creation of 'customized' paths:

- Available in 40 mm or 60 mm diameter tubing,
- Various post types: straight, corner, 2-sided or 3-sided,
- Various gate types: wicket gate or swing gate

Fixings available as options.







Customs code	7326909890
EAN	3321360116956

Color : Yellow

Material : Galvanized steel

Specifications :

- Swing gate with one-way opening, compatible with modular barrier.
- Tube diameter 60 mm.
- Fitted with 2 removable catches to secure the door if required.
- Compatible with the BTC60STOP stop post, which allows the door to be secured in the closed position.
- Offset fixing plate 150 x 60 mm with 4 holes Ø 14 mm.
- Fixings optional.
- Do not install in saline or hydrocarbon environments.

Length (mm)	Width (mm)	Height (mm)	Dimensions plate (mm)	Net weight (kg)
1022	170	1000	170 x 80	12,20

VISO
www.viso-cpn.com

VISO - 7 avenue Arago - ZI de la Vigne aux Loups - 91380 CHILLY-MAZARIN - France
Tél. + 33 (0)1 69 53 46 70 - Fax + 33 (0)1 69 53 46 80 - contact@viso-cpn.com / commande@viso-cpn.com