



FAG

6244-M [🔗](#)

Deep groove ball bearing

Deep groove ball bearing 62...-M, single row,
solid brass cage

Technical information



Your current product variant

Sealing	Without	Not sealed
Cage	M	Solid brass cage, rolling element guided
Tolerance class	PN	Normal (PN)
Dimensional / heat stabilization	S1	Rings dimensional stabilized up to 200°
Lubricant	Without	Bearing not greased
Radial internal clearance	CN (Group N)	Normal internal clearance
Bore type	Z	Cylindrical

Main Dimensions & Performance Data

d	220 mm	Bore diameter
D	400 mm	Outside diameter
B	65 mm	Width
C _r	295,000 N	Basic dynamic load rating, radial
C _{0r}	355,000 N	Basic static load rating, radial
C _{ur}	13,900 N	Fatigue load limit, radial
n _G	2,850 1/min	Limiting speed
n _{gr}	2,200 1/min	Reference speed
≈m	37.9 kg	Weight



Mounting dimensions

$d_{a\min}$	237 mm	Minimum diameter shaft shoulder
$D_{a\max}$	383 mm	Maximum diameter of housing shoulder
$r_{a\max}$	3 mm	Maximum fillet radius

Dimensions

$r_{\min}$	4 mm	Minimum chamfer dimension
D_1	337.7 mm	Shoulder diameter outer ring
d_1	282.1 mm	Shoulder diameter inner ring

Temperature range

$T_{\min}$	-30 °C	Operating temperature min.
$T_{\max}$	200 °C	Operating temperature max.

Calculation factors

f_0	15.2	Calculation factor
-------	------	--------------------

Characteristics

	Radial load
	Axial load in one direction
	Axial load in two directions
	Grease Lubrication
	Oil Lubrication
	Not sealed
	Large bearing