

Chassis Monitor



10.4"

Specifications




Model Name	R10L200-CHU1
Viewable Size Image	10.4"
Active Display Area(mm)	211.2(H)x158.4(V)
Pixel Pitch(mm)	0.264(H)x0.264(V)(typ.)
Number of Pixels	800x600
Contrast Ratio	600:1(typ.)
Display Color	16.2M(8bit/colors)
Brightness(cd/m ²)	230
Viewing Angle(CR>=10)	-70~70(H);-55~65(V)(typ.)
Synchronization Range	31.5~46.9KHz/60~75Hz
Horizontal/Vertical	
Recommended Resolution	800x600@60Hz, 75Hz
Signal Connector	15 pin D-Sub
Power Source	AC100~240V, Universal, ±10%
Power Consumption	15W typical, normal operation
Power Management	VESA DPMS Compliant
Plug & Play	VESA DDC 1/2B
Optional Video Input	S-Video, Composite
Optional DVI Input	No
Optional Touch Screen	Resistive, SAW, IR

Remarks:R10L200 series= VGA input only

R10L230 series= VGA+Video Input

*Optional Touch Screen requires different mechanical design.

Mechanical Drawing



* Note: this is a simplified drawing and some components are not marked in detail. Please contact our sales representative if you need further product information.



Rev.	Reasons	Revised Date
1.0	Spec change	Apr-23-09
1.1	Spec change	Sep-09-11