



# Product data sheet

Power tools for trade & industry

Random Orbit Sander

## PRO GEX 34-150



Robust 150mm random orbit sander with high removal rate

### The most important data

Rated input power	340 W
Sanding pad diameter	150 mm
Orbit diameter	4 mm

**Order number** 0 601 372 870

## Technical data

### Additional data

Rated input power	340 W
Sanding pad diameter	150 mm
Orbit diameter	4 mm
Voltage, electrical	240 V
Weight	2.1 kg
No-load speed	4,500 – 12,000 rpm
Orbital stroke rate	9,000 – 24,000 opm
Eccentricity	2 mm

## Noise/vibration information

### Sanding solid wood

Vibration emission value ah	5 m/s <sup>2</sup>
Uncertainty K	1.5 m/s <sup>2</sup>



# Product data sheet

Power tools for trade & industry

---

## Advantages:

- Constant speed and high removal rate for efficient results even on demanding surfaces
- Aluminium bearing flange ensures a long tool lifetime and makes it ideal for use on tough applications
- Multi-hole sanding pad for sanding sheets with different hole pattern and for significantly increased dust extraction

**HEAVY  
DUTY**

---

You can find more information about the deviations in the following link: <https://www.bosch-professional.com/kw/en/wac/>

